


# TR2439



## Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/



- 1 LEDs Display unit / Switching status
- 2 alphanumeric display 4-digit red/green
- 3 Programming buttons



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1	
Measuring range	-100...600 °C	-148...1112 °F
Communication interface	IO-Link	
Process connection	threaded connection G 1/2 external thread	

### Application

System	gold-plated contacts
Application	for Pt100 and Pt1000 measuring elements

### Electrical data

Operating voltage	[V]	18...32 DC; (cULus - Class 2 source required)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Integrated watchdog		yes

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
------------------------------	---

### Outputs

Total number of outputs	2
Output signal	switching signal; analog signal; IO-Link; (configurable)
Electrical design	PNP/NPN

# TR2439



## Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

Number of digital outputs

1

Output function

normally open / closed; (configurable)

Max. voltage drop switching output DC [V]

2.5

Permanent current rating of switching output DC [mA]

250

Number of analog outputs

1

Analog current output [mA]

4...20

Max. load [Ω]

500

Analog voltage output [V]

0...10

Min. load resistance [Ω]

2000

Short-circuit protection

yes

Type of short-circuit protection

yes (non-latching)

Overload protection

yes

### Measuring/setting range

Measuring range	-100...600 °C	-148...1112 °F
-----------------	---------------	----------------

Factory setting	-40...300 °C / -40...572 °F	
-----------------	-----------------------------	--

Set point SP	-99.8...600 °C	-147.6...1112 °F
--------------	----------------	------------------

Reset point rP	-100...599.8 °C	-148...1111.6 °F
----------------	-----------------	------------------

Analog start point	-100...595 °C	-148...1103 °F
--------------------	---------------	----------------

Analog end point	-95...600 °C	-139...1112 °F
------------------	--------------	----------------

In steps of	0.1 °C	0.1 °F
-------------	--------	--------

### Resolution

Resolution of switching output	[K]	0.1
--------------------------------	-----	-----

Resolution of analog output	[K]	current output: MS / 4096; voltage output: MS / 3561
-----------------------------	-----	--

Resolution of display	[K]	0.1
-----------------------	-----	-----

### Accuracy / deviations

Switch point accuracy	[K]	± 0,3 + (± 0,1 % MS)
-----------------------	-----	----------------------

Precision analog output	[K]	± 0,3 + (± 0,1 % MS)
-------------------------	-----	----------------------

Display accuracy	[K]	± 0,3 + (± 0,1 % MS)
------------------	-----	----------------------

Temperature coefficient	[% of the span / 10 K]	0,1; (In case of deviation from the reference condition 25 ± 5 °C)
-------------------------	------------------------	--

### Reaction times

Response time	[ms]	390
---------------	------	-----

Max. response time analog output	[ms]	390
----------------------------------	------	-----

### Software / programming

Parameter setting options	hysteresis / window; normally open / closed; switch-on/switch-off delay; Damping; Display unit; current/voltage output
---------------------------	--

### Interfaces

Communication interface	IO-Link
-------------------------	---------

Transmission type	COM2 (38,4 kBaud)
-------------------	-------------------

IO-Link revision	1.1
------------------	-----

# TR2439



## Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

### Operating conditions

Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

### Tests / approvals

EMC	DIN EN 61000-6-3	
	DIN EN 61000-6-2	
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]		233
UL approval	UL approval number	K011

### Mechanical data

Weight [g]	200
Material	stainless steel (1.4404 / 316L); stainless steel (1.4301 / 304); PBT+PC-GF30; PBT-GF20; PC
Process connection	threaded connection G 1/2 external thread

### Displays / operating elements

Display	Display unit	2 x LED, green
	Switching status	LED, yellow
	Measured values	alphanumeric display, red/green 4-digit

### Remarks

Remarks	MS = set measuring span
Pack quantity	1 pcs.

### Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



## Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

### Connection



OUT1:           Switching output / IO-Link  
OUT2:           analog output  
                  Colors to DIN EN 60947-5-2