


TS2452



Temperature cable sensor with process connection

TS-200KLKD06 .../US



1 connection area, see remark



Product characteristics

Measuring range	-100...600 °C	-148...1112 °F
Process connection	Ø 6 mm	
Installation length EL [mm]	100; (medium temperatures < 200 °C: 150)	

Application

Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Media	liquids and gases
Minimum installation depth [mm]	15

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	150	
Measuring range		-100...600 °C	-148...1112 °F

Accuracy / deviations

Accuracy [K]	± (0,15 K + 0,002 x t)
--------------	-------------------------

Reaction times

Dynamic response T05 / T09 [s]	12 / 34; (according to DIN EN 60751)
--------------------------------	--------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF [years]	11415.5
--------------	---------

Mechanical data

Weight [g]	87
Dimensions [mm]	Ø 6
Material	stainless steel (1.4571/316Ti); PFA/PTFE
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	Ø 6 mm
Probe diameter [mm]	6
Installation length EL [mm]	100; (medium temperatures < 200 °C: 150)

Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

TS2452



Temperature cable sensor with process connection

TS-200KLKD06 .../US

Electrical connection

Cable: 2 m, PTFE; temperature-resistant up to 250°C

Connector: 1 x M12; coding: A



Connection

