


TS2789



Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/2M PUR



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	threaded connection M5 external thread	

Application

System	gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Installation	Contact sensor for solid bodies

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy	[K]	$\pm (0,15 K + 0,002 \times t)$
----------	-----	-----------------------------------

Reaction times

Dynamic response T05 / T09	[s]	3 / 8; (according to DIN EN 60751)
----------------------------	-----	------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	11415.5

Mechanical data

Weight	[g]	80.95
Housing	screw-in sensor	
Dimensions	[mm]	M5 / L = 26
Thread designation	M5	
Material	stainless steel (1.4404 / 316L)	
Tightening torque	[Nm]	1.5
Process connection	threaded connection M5 external thread	

Remarks

Pack quantity	1 pcs.
---------------	--------

TS2789



Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/2M PUR

Electrical connection

Cable: 2 m, PUR

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

