


TS4759



Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/4M



Product characteristics

Measuring range	-30...180 °C	-22...356 °F
Process connection	threaded connection M5 external thread	

Application

Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Installation	Contact sensor for solid bodies

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-30...180 °C	-22...356 °F
-----------------	--------------	--------------

Accuracy / deviations

Accuracy	[K]	± (0,15 K + 0,002 x t)
----------	-----	-------------------------

Reaction times

Dynamic response T05 / T09	[s]	3 / 8; (according to DIN EN 60751)
----------------------------	-----	------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF	[years]	12683.9
------	---------	---------

Mechanical data

Weight	[g]	159.6
Housing	screw-in sensor	
Dimensions	[mm]	M5
Thread designation	M5	
Material	stainless steel (1.4404 / 316L)	
Process connection	threaded connection M5 external thread	

Remarks

Pack quantity	1 pcs.	
---------------	--------	--

TS4759




Temperature cable sensor with screw-in sensor

TS-PT100-SCREW-IN M5/4M

Electrical connection

Cable: 4 m, silicone

Connection



RD =

WH =

Core colors :

red

white