


# TS9256



## Temperature cable sensor with process connection

TS-015KIKD06...../US



### Product characteristics

Measuring range	-50...250 °C	-58...482 °F
Process connection	Ø 6 mm	
Installation length EL [mm]	50	

### Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Minimum installation depth [mm]	15

### Electrical data

Protection class	III
------------------	-----

### Measuring/setting range

Probe length L	[mm]	50	
Measuring range		-50...250 °C	-58...482 °F
Note on measuring range		stationary: 280 °C / 536 °F (10000 h)	

### Accuracy / deviations

Accuracy [K]	± (0,15 K + 0,002 x t )
--------------	-------------------------

### Reaction times

Dynamic response T05 / T09 [s]	11 / 37; (according to DIN EN 60751)
--------------------------------	--------------------------------------

### Operating conditions

Protection	IP 67
------------	-------

### Tests / approvals

MTTF [years]	11415.5
--------------	---------

### Mechanical data

Weight [g]	26.4
Dimensions [mm]	Ø 6
Material	stainless steel (1.4571/316Ti ); PFA/PTFE
Materials (wetted parts)	stainless steel (1.4571/316Ti )
Process connection	Ø 6 mm
Probe diameter [mm]	6
Installation length EL [mm]	50

### Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

# TS9256



## Temperature cable sensor with process connection

TS-015KIKD06...../US

### Electrical connection

Cable: 0.15 m, PTFE

Connector: 1 x M12; coding: A



### Connection

