


TS9289



Temperature cable sensor with process connection

TS-250KDK6-...../US/



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	Ø 6 mm	

Application

System	gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Media	liquids and gases
Minimum installation depth [mm]	15

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 x t)$
--------------	-----------------------------

Reaction times

Dynamic response T05 / T09 [s]	3 / 10; (according to DIN EN 60751)
--------------------------------	-------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF [years]	11415.5
--------------	---------

Mechanical data

Weight [g]	95.45
Housing	Measuring probes
Dimensions [mm]	Ø 6 / L = 45
Material	stainless steel
Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	Ø 6 mm
Probe diameter [mm]	6

Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

TS9289



Temperature cable sensor with process connection

TS-250KLKD6-...../US/

Electrical connection

Cable: 2.5 m, PUR

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

