


Flow meter with fast response and display

SBG32KM0FRKG



CRN cUL us LISTED

Product characteristics

Measuring range	4...200 l/min	0.24...12 m³/h	65...3170 gph	1.1...52.8 gpm
Process connection	threaded connection G 1 1/2 Internal thread			
Application				
System	gold-plated contacts			
Media	Liquids; oils (viscosity 10 mm²/s at 40 °C)			
Medium temperature [°C]	-10...100			
Pressure rating [bar]	63			
Pressure rating [MPa]	6.3			
Note on pressure rating	at medium temperature >70°C: 50 bar / 5 MPa			

SB1257

Flow meter with fast response and display

SBG32KM0FRKG



Electrical data				
Operating voltage	[V]		18...30 DC; (to SELV/PELV)	
Current consumption	[mA]		< 50	
Protection class			III	
Reverse polarity protection			yes	
Power-on delay time	[s]		< 3	
Outputs				
Total number of outputs			2	
Output signal			switching signal; analog signal; frequency signal; IO-Link	
Output function			normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]		2	
Max. current load per output	[mA]		150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)	
Analog current output	[mA]		4...20	
Max. load	[Ω]		500	
Short-circuit protection			yes	
Overload protection			yes	
Frequency of the output	[Hz]		0...10000	
Measuring/setting range				
Measuring range	4...200 l/min	0.24...12 m³/h	65...3170 gph	1.1...52.8 gpm
Display range	0...240 l/min	0...14.4 m³/h	0...3805 gph	0...63.4 gpm
Resolution	0.1 l/min	0.01 m³/h	1 gph	0.1 gpm
Set point SP	1.4...200 l/min	0.08...12 m³/h	20...3170 gph	0.3...52.8 gpm
Reset point rP	0...198.6 l/min	0...11.92 m³/h	0...3150 gph	0...52.5 gpm
Frequency end point, FEP	13.4...200 l/min	0.8...12 m³/h	210...3170 gph	3.5...52.8 gpm
In steps of	0.02 l/min	0.02 m³/h	5 gph	0.1 gpm
Frequency at the end point FRP			10...10000	
In steps of	[Hz]		10	
Measuring dynamics			1:50	
Temperature monitoring				
Measuring range	-10...100 °C		14...212 °F	
Display range	-32...122 °C		-25.6...251.6 °F	
Resolution	0.1 °C		0.1 °F	
Set point SP	-9.3...100 °C		15.2...212 °F	
Reset point rP	-10...99.3 °C		14...210.8 °F	
In steps of	0.1 °C		0.2 °F	
Frequency start point, FSP	-10...78 °C		14...172.4 °F	
Frequency end point, FEP	12...100 °C		53.6...212 °F	
Frequency at the end point FRP			10...10000	
In steps of	[Hz]		10	
Accuracy / deviations				
Flow monitoring				
Accuracy (in the measuring range)			± 5 % MEW; (Q > 1 l/min; 20...70 °C Medium temperature)	

SB1257



Flow meter with fast response and display

SBG32KM0FRKG

Repeatability		± 1 % MEW
Temperature monitoring		
Temperature drift		0,029 °C / K
Accuracy	[K]	3 K (25°C; Q > 1 l/min)
Reaction times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analog output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color; calibration factor	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1047
Operating conditions		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	145
UL approval	UL approval number	I007
Pressure equipment directive	sound engineering practice	

SB1257




Flow meter with fast response and display

SBG32KM0FRKG

Mechanical data				
Weight	[g]	2796.5		
Material		stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated		
Materials (wetted parts)		stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM		
Process connection		threaded connection G 1 1/2 Internal thread		
Switching cycles mechanical		10 million		
Displays / operating elements				
Display	Display unit	6 x LED, green		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, red/green alternating indication 4-digit		
	Programming	alphanumeric display, 4-digit		
Remarks				
Remarks	<p>Use of 200 micron filtration is recommended. All data refer to oil with the following nominal viscosity: 10 mm²/s, 40 °C MW = Measured value MEW = Final value of the measuring range</p>			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				
				

Flow meter with fast response and display

SBG32KM0FRKG

Connection**OUT1:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

OUT2:

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

- | | |
|------|-------|
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |

Diagrams and graphs