


SB7243



Flow meter with fast response and display

SBG11KL0FRKG



Product characteristics

Measuring range	1...25 l/min	0.06...1.5 m³/h	16...396.5 gph	0.26...6.6 gpm
Process connection	threaded connection G 1 Internal thread			

Application

System	gold-plated contacts
Media	Liquids; oils (viscosity 320 mm²/s at 40 °C)
Medium temperature [°C]	-10...100
Pressure rating [bar]	100
Pressure rating [MPa]	10
Note on pressure rating	at medium temperature >70°C: 80 bar / 8 MPa

SB7243



Flow meter with fast response and display

SBG11KL0FRKG

Electrical data					
Operating voltage	[V]	18...30 DC; (to SELV/PELV ; cULus - Class 2 source required)			
Current consumption	[mA]	< 50			
Protection class		III			
Reverse polarity protection		yes			
Power-on delay time	[s]	< 3			
Outputs					
Total number of outputs		2			
Output signal		switching signal; analog signal; frequency signal; IO-Link			
Max. voltage drop switching output DC	[V]	2			
Max. current load per output	[mA]	150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)			
Analog current output	[mA]	4...20			
Max. load	[Ω]	500			
Short-circuit protection		yes			
Overload protection		yes			
Frequency of the output	[Hz]	0...10000			
Measuring/setting range					
Measuring range	1...25 l/min	0.06...1.5 m³/h	16...396.5 gph	0.26...6.6 gpm	
Display range	0...30 l/min	0...1.8 m³/h	0...475.5 gph	0...7.93 gpm	
Resolution	0.01 l/min	0.001 m³/h	0.1 gph	0.001 gpm	
Set point SP	0.16...25 l/min	0.01...1.5 m³/h	2.5...396 gph	0.04...6.6 gpm	
Reset point rP	0...24.84 l/min	0...1.49 m³/h	0...393.5 gph	0...6.56 gpm	
Frequency end point, FEP	1.66...25 l/min	0.1...1.5 m³/h	25.6...396 gph	0.44...6.6 gpm	
In steps of	0.02 l/min	0.002 m³/h	0.5 gph	0.01 gpm	
Frequency at the end point FRP		10...10000			
In steps of	[Hz]	10			
Measuring dynamics		1:50			
Temperature monitoring					
Measuring range	-10...100 °C	14...212 °F			
Display range	-32...122 °C	-25.6...251.6 °F			
Resolution	0.1 °C	0.1 °F			
Set point SP	-9.3...100 °C	15.2...212 °F			
Reset point rP	-10...99.3 °C	14...210.8 °F			
In steps of	0.1 °C	0.2 °F			
Frequency start point, FSP	-10...78 °C	14...172.4 °F			
Frequency end point, FEP	12...100 °C	53.6...212 °F			
Frequency at the end point FRP	[Hz]	10...10000			
Accuracy / deviations					
Flow monitoring					
Accuracy (in the measuring range)		± 5 % MEW; (Q > 1 l/min; 20...70 °C Medium temperature)			
Repeatability		± 1 % MEW			

SB7243



Flow meter with fast response and display

SBG11KL0FRKG

Temperature monitoring		
Temperature drift		0,029 °C / K
Accuracy	[K]	3 K (25°C; Q > 1 l/min)
Reaction times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analog output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color; calibration factor	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1044
Operating conditions		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C	
	medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	170
UL approval	UL approval number	I006
	File number UL	E174189
Pressure equipment directive	sound engineering practice	

SB7243

Flow meter with fast response and display

SBG11KL0FRKG




Mechanical data				
Weight	[g]	1604		
Material		stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated		
Materials (wetted parts)		stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM		
Process connection		threaded connection G 1 Internal thread		
Switching cycles mechanical		10 million		
Displays / operating elements				
Display	Display unit	6 x LED, green		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, red/green alternating indication 4-digit		
	Programming	alphanumeric display, 4-digit		
Remarks				
Remarks	<p>Use of 200 micron filtration is recommended.</p> <p>All data refer to oil with the following nominal viscosity: 320 mm²/s, 40 °C</p> <p>MW = Measured value</p> <p>MEW = Final value of the measuring range</p>			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				



Flow meter with fast response and display

SBG11KL0FRKG

Connection**OUT1:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

OUT2:

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

BK =	black
BN =	brown
BU =	blue
WH =	white

Diagrams and graphs