


Flow meter with fast response and display

SBG32KM0FRKG



Product characteristics

Measuring range	8...200 l/min	0.48...12 m³/h	130...3170 gph	2.1...52.8 gpm
Process connection	threaded connection G 1 1/2 Internal thread			
Application				
System	gold-plated contacts			
Media	Liquids; oils (viscosity 320 mm²/s at 40 °C)			
Medium temperature [°C]	-10...100			
Pressure rating [bar]	63			
Pressure rating [MPa]	6.3			
Note on pressure rating	at medium temperature >70°C: 50 bar / 5 MPa			

SB7257



Flow meter with fast response and display

SBG32KM0FRKG

Electrical data					
Operating voltage	[V]	18...30 DC; (to SELV/PELV ; cULus - Class 2 source required)			
Current consumption	[mA]	< 50			
Protection class		III			
Reverse polarity protection		yes			
Power-on delay time	[s]	< 3			
Outputs					
Total number of outputs		2			
Output signal		switching signal; analog signal; frequency signal; IO-Link			
Output function		normally open / closed; (configurable)			
Max. voltage drop switching output DC	[V]	2			
Max. current load per output	[mA]	150; (200: ...60 °C; Ambient temperature; 250: ...40 °C; Ambient temperature)			
Analog current output	[mA]	4...20			
Max. load	[Ω]	500			
Short-circuit protection		yes			
Overload protection		yes			
Frequency of the output	[Hz]	0...10000			
Measuring/setting range					
Measuring range	8...200 l/min	0.48...12 m³/h	130...3170 gph	2.1...52.8 gpm	
Display range	0...240 l/min	0...14.4 m³/h	0...3805 gph	0...63.4 gpm	
Resolution	0.1 l/min	0.01 m³/h	1 gph	0.1 gpm	
Set point SP	1.4...200 l/min	0.08...12 m³/h	20...3170 gph	0.3...52.8 gpm	
Reset point rP	0...198.6 l/min	0...11.92 m³/h	0...3150 gph	0...52.5 gpm	
Frequency end point, FEP	13.4...200 l/min	0.8...12 m³/h	210...3170 gph	3.5...52.8 gpm	
In steps of	0.02 l/min	0.02 m³/h	5 gph	0.1 gpm	
Frequency at the end point FRP		10...10000			
In steps of	[Hz]	10			
Measuring dynamics		1:50			
Temperature monitoring					
Measuring range	-10...100 °C	14...212 °F			
Display range	-32...122 °C	-25.6...251.6 °F			
Resolution	0.1 °C	0.1 °F			
Set point SP	-9.3...100 °C	15.2...212 °F			
Reset point rP	-10...99.3 °C	14...210.8 °F			
In steps of	0.1 °C	0.2 °F			
Frequency start point, FSP	-10...78 °C	14...172.4 °F			
Frequency end point, FEP	12...100 °C	53.6...212 °F			
Frequency at the end point FRP		10...10000			
In steps of	[Hz]	10			
Accuracy / deviations					
Flow monitoring					
Accuracy (in the measuring range)		± 5 % MEW; (Q > 1 l/min; 20...70 °C Medium temperature)			

SB7257



Flow meter with fast response and display

SBG32KM0FRKG

Repeatability		± 1 % MEW
Temperature monitoring		
Temperature drift		0,029 °C / K
Accuracy	[K]	3 K (25°C; Q > 1 l/min)
Reaction times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
In steps of	[s]	0.1
Damping for the analog output dAA	[s]	0...5
In steps of	[s]	0.1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/frequency output; damping for the switching output / analog output; display can be rotated and switched off; standard unit of measurement; process value color; calibration factor	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	Type of operation	DeviceID
	default	1047
Operating conditions		
Ambient temperature	[°C]	0...60
Note on ambient temperature	medium temperature < 80 °C medium temperature < 100 °C: 0...40 °C	
Storage temperature	[°C]	-15...80
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2 DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	145
UL approval	UL approval number	I007
	File number UL	E174189

SB7257



Flow meter with fast response and display

SBG32KM0FRKG

Pressure equipment directive

sound engineering practice

Mechanical data

Weight	[g]	2810.2
Material		stainless steel (1.4404 / 316L); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated
Materials (wetted parts)		stainless steel (1.4401 / 316); stainless steel (1.4404 / 316L); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM
Process connection		threaded connection G 1 1/2 Internal thread
Switching cycles mechanical		10 million

Displays / operating elements

Display	Display unit	6 x LED, green
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, red/green alternating indication 4-digit
	Programming	alphanumeric display, 4-digit

Remarks

Remarks	Use of 200 micron filtration is recommended.
	All data refer to oil with the following nominal viscosity: 320 cSt, 40 °C ± 3 K
	MW = Measured value
	MEW = Final value of the measuring range

Pack quantity

1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Flow meter with fast response and display

SBG32KM0FRKG

Connection**OUT1:**

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- Frequency output Volumetric flow quantity monitoring
- Frequency output Temperature monitoring
- IO-Link

OUT2:

- Switching output Volumetric flow quantity monitoring
- Switching output Temperature monitoring
- analog output Volumetric flow quantity monitoring
- analog output Temperature monitoring
- Colors to DIN EN 60947-5-2

Core colors :

BK =	black
BN =	brown
BU =	blue
WH =	white

Diagrams and graphs