
### Flow sensor with fast response time





Process connection		threaded connection G 1/2	
Application			
Media		Liquids; water; glycol solutions; Coolants	
Medium temperature	[°C]	085	
Pressure rating	[bar]	40	
Pressure rating	[MPa]	4	
Electrical data			
Operating voltage	[V]	1030 DC; (to SELV/PELV)	
Current consumption	[mA]	< 15	

### Flow sensor with fast response time



Protection class	III		
Reverse polarity protection	yes		
Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 1		
Outputs			
Total number of outputs	1		
Output signal	switching signal		
Electrical design	PNP		
Number of digital outputs	1		
Output function	normally open		
Max. voltage drop switching [V] output DC	2.5		
Permanent current rating of [mA] switching output DC	100		
Short-circuit protection	yes		
Overload protection	yes		
Measuring/setting range			
Setting range [I/min]	115		
Accuracy / deviations			
Repeatability	1		
[% of the final value]			
Hysteresis [l/min]	0,21		
Measuring error [% of the final value]	± 5		
Reaction times			
Response time [s]	< 0.01		
Operating conditions			
Ambient temperature [°C]	060		
Storage temperature [°C]	-1580		
Protection	IP 65; IP 67		
Tests / approvals			
EMC	DIN EN 61000-6-2		
	DIN EN 61000-6-3		
Shock resistance	DIN EN 60068-2-27 20 g (11 ms)		
Vibration resistance	DIN EN 60068-2-6 5 g (102000 Hz)		
MTTF [years]	3318		
Mechanical data			
Weight [g]	533.5		
Material	brass chemically nickel-plated; PPS; aluminum anodized; PA		
Materials (wetted parts)	stainless steel (1.4310 / 301); stainless steel (1.4301 / 304); PBT; brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM		
Process connection	threaded connection G 1/2		
Switching cycles mechanical	10 million		

### Flow sensor with fast response time



Displays / operating elements Display	Switching status	4 x LED, yellow	
Accessories	Switching status		
Items supplied		Allen key	
		Allen key	
Remarks	Coution Do not turn	the can have and the maximum value of the acting range	
Remarks	Caution Do not turn the cap beyond the maximum value of the setting range. All data refer to water (20 °C).		
Notes	Please note the changed housing design!		
Pack quantity	1 pcs.		
		1 μcs.	
Electrical connection			
Connector: 1 x M12; coding: A			
2 3 4 Connection			
Connection			
		$\frac{1}{3} \qquad L^+$	

### Flow sensor with fast response time



