
SBU625

Flow transmitters with fast response time

SBU12DI040KG/US







Product characteristics				
Measuring range	[l/min]	0.375		
Process connection		G 1/2		
Application				
Application		Machine tools; Internal cooling of drill		
Media		Liquids; water; glycol solutions; Coolants		
Medium temperature	[°C]	060		
Pressure rating	[bar]	200		
Pressure rating	[MPa]	20		
Electrical data				
Operating voltage tolerance	[%]	-1510		
Operating voltage	[V]	24 DC; (to SELV/PELV)		
Current consumption	[mA]	10		
Protection class		III		
Reverse polarity protection		yes		
Outputs				
Output signal		analog signal		
Analog voltage output	[V]	0.510		
Min. load resistance	[Ω]	10000		
Short-circuit protection		yes		
Overload protection		yes		


SBU625

Flow transmitters with fast response time





Measuring/setting range					
Measuring range	[l/min]	0.375			
Flow range	[l/min]	75			
Accuracy / deviations					
Repeatability					
[% of the final value]		1			
Measuring error		± 5			
[% of the final value]					
Reaction times					
Response time	[s]	< 0.01			
Operating conditions					
Ambient temperature	[°C]	060			
Storage temperature	[°C]	-1580			
Protection		IP 65; IP 67			
Tests / approvals					
EMC		DIN EN 61000-6-2			
		DIN EN 61000-6-3			
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)		
Vibration resistance		DIN EN 60068-2-6	5 g (102000 Hz)		
MTTF	[years]	15.78			
Mechanical data					
Weight	[g]	738			
Material		aluminum anodized; PA			
Materials (wetted parts)		stainless steel (1.4401 / 316); brass; aluminum anodized; PU; O-ring: FKM			
Process connection		G 1/2			
Switching cycles mechanical		10 million			
Accessories					
Items supplied		sealing plug			
Remarks					
Remarks		Temperature changes affect the specified standard settings for coolants.			
		For oils, the settings are influenced by temperature and viscosity.			
		Recommendation Use 200 micron filtration			
		All data refer to coolants (20 °C).			
Pack quantity		1 pcs.			
Electrical connection					
Connector: 1 v M12: cod	lina: A				



Connector: 1 x M12; coding: A




SBU625

Flow transmitters with fast response time





Connection



Colors to DIN EN 60947-5-2

Core colors :

BN = brown BU = blue WH = white

Diagrams and graphs

