Flow sensor with fast response time

SBY12IR0BPKG/US



Please note the changed housing design! M8x6/8 M12 M12 G6,5 106...113

ϵ

Product characteristics			
Number of inputs and outputs		Number of digital outputs: 1	
Process connection		Rp 1/2	
Application			
Media		Liquids; water; glycol solutions; Coolants	
Medium temperature	[°C]	085	
Pressure rating	[bar]	80	
Pressure rating	[MPa]	8	
Electrical data			
Operating voltage	[V]	1030 DC; (to SELV/PELV)	
Current consumption	[mA]	< 15	
Protection class		III	
Reverse polarity protection		yes	

Flow sensor with fast response time





Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 1		
Outputs				
Total number of outputs			1	
Output signal			ng signal	
Electrical design			NP	
Number of digital outputs			1	
Output function		normally open		
Max. voltage drop switching output DC	j [V]	2.5		
Permanent current rating of switching output DC	[mA]	100		
Short-circuit protection		У	es	
Overload protection		У	es	
Measuring/setting range				
Setting range	[l/min]	0.2	24	
Accuracy / deviations				
Repeatability			1	
[% of the fin		1		
Hysteresis	[l/min]	0,1.	0,2	
Measuring error	-1	±5		
[% of the fin	ai valuej			
Reaction times	r-1			
Response time	[s]	<(0.01	
Operating conditions	1001			
Ambient temperature	[°C]	060		
Storage temperature	[°C]	-1580		
Protection		IP 65; IP 67		
Tests / approvals		DIVI 5N 04000 0 0		
EMC		DIN EN 61000-6-2 DIN EN 61000-6-3		
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)	
Vibration resistance		DIN EN 60068-2-6	5 g (102000 Hz)	
MTTF	[years]		387	
Mechanical data				
Weight	[g]	474	4.05	
Material		brass chemically nickel-plated; aluminum anodized; PA		
Materials (wetted parts)		stainless steel (1.4310 / 301); stainless steel (1.4401 / 316); PBT; brass chemically nickel-plated; PPS; O-ring: FKM Polyolefin		
Process connection		Rp 1/2		
Switching cycles mechanical		10 million		
Displays / operating elements				
Display		Switching status	4 x LED, yellow	

Flow sensor with fast response time






Accessories		
Items supplied	Allen key	
Remarks		
Remarks	Caution Do not turn the setting screw beyond the maximum value of the setting range.	
	All data refer to water (20 °C).	
Notes	Please note the changed housing design!	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A



Connection



Flow sensor with fast response time





