


# TT7281



## Temperature probe sensor

TT-070KFBD06- /US/



L = Probe length corresponds to installation length EL



Product characteristics		
Measuring range	-40...150 °C	-40...302 °F
Process connection	Clamp fitting Ø 6 mm	
Installation length EL [mm]	70	
Application		
Special feature	gold-plated contacts	
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating	160 bar	16 MPa
Minimum installation depth [mm]	15	
Electrical data		
Protection class	III	
Measuring/setting range		
Probe length L [mm]	70	
Measuring range	-40...150 °C	-40...302 °F
Accuracy / deviations		
Accuracy [K]	± (0,15 K + 0,002 x t )	
Reaction times		
Dynamic response T05 / T09 [s]	1 / 3; (according to DIN EN 60751)	
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 68; IP 69K	
Tests / approvals		
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
Mechanical data		
Weight [g]	28.8	
Housing	tubular	
Dimensions [mm]	Ø 6 / L = 94	
Material	stainless steel (1.4404 / 316L)	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	

# TT7281



## Temperature probe sensor

TT-070KFBD06- /US/

Process connection		Clamp fitting Ø 6 mm
Probe diameter	[mm]	6
Installation length EL	[mm]	70

### Remarks

Remarks	cULus - Class 2 source required The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

