
#### Flow sensor with fast response time

SBY34BF0BPKG/US



### Please note the changed housing design!





Product characteristics				
Number of inputs and outputs		Number of digital outputs: 1		
Process connection		Rp 3/4		
Application				
Media		Liquids; water; glycol solutions; Coolants		
Medium temperature	[°C]	085		
Pressure rating	[bar]	40		
Pressure rating	[MPa]	4		
Electrical data				
Operating voltage	[V]	1030 DC; (to SELV/PELV)		
Current consumption	[mA]	< 15		
Protection class		III		
Reverse polarity protection		yes		

### Flow sensor with fast response time





Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 1	
Outputs			S 4
Total number of outputs			1
Output signal			ng signal
Electrical design			NP
Number of digital outputs			1
Output function			- lly open
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	1	00
Short-circuit protection		у	es
Overload protection		у	es
Measuring/setting range			
Setting range	[l/min]	1	15
Accuracy / deviations			
Repeatability			1
[% of the fin	al value]		1
Hysteresis	[l/min]	0,2	21
Measuring error		<u>+</u>	: 5
[% of the fin	al value]		
Reaction times	1		
Response time	[s]	<(	0.01
Operating conditions			
Ambient temperature	[°C]	060	
Storage temperature	[°C]	-1580	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		DIN EN 61000-6-2	
Shock resistance		DIN EN 61000-6-3 DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance		DIN EN 60068-2-27 DIN EN 60068-2-6	5 g (102000 Hz)
MTTF	[years]		318
Mechanical data	- 1		
Weight	[g]	 55	9.6
Material	103	brass chemically nickel-plated; PP; aluminum anodized; PA	
Materials (wetted parts)		stainless steel (1.4310 / 301); stainless steel (1.4301 / 304); PBT; brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM	
Process connection		Rp 3/4	
Switching cycles mechanical		10 million	
Displays / operating elements			
Display		Switching status	4 x LED, yellow
			-

#### Flow sensor with fast response time






Accessories			
Items supplied	Allen key		
Remarks			
Remarks	Caution Do not turn the cap beyond the maximum value of the setting range.		
	All data refer to water (20 °C).		
Notes	Please note the changed housing design!		
Pack quantity	1 pcs.		

### Electrical connection

Connector: 1 x M12; coding: A



#### Connection



#### Flow sensor with fast response time





