


Infrared temperature sensor

TW-150KLBM30-KFDKG/US



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1	
Measuring range	500...2500 °C	932...4532 °F
Communication interface	IO-Link	

Application

Application	tempering temperatures; glass melting; graphite; ceramics; metals; forging; sintering; heat treatment; rolling
-------------	--

Electrical data

Operating voltage	[V]	18...32 DC; (to SELV/PELV)
Current consumption	[mA]	< 50
Min. insulation resistance	[MΩ]	100; (50 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 1

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
------------------------------	---

Inputs

Test input	type 3 (IEC 61131-2)
------------	----------------------

Outputs

Total number of outputs	2
Output signal	switching signal; analog signal; IO-Link; (configurable)
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC	[V] 2.5
Permanent current rating of switching output DC	[mA] 150
Number of analog outputs	1
Analog current output	[mA] 4...20

TW2002



Infrared temperature sensor

TW-150KLBM30-KFDKG/US

Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Short-circuit proof		yes
Overload protection		yes
Monitoring range		
Wave length range	[μm]	0.78...1.06
Measuring/setting range		
Measuring range	500...2500 °C	932...4532 °F
Set point SP	502...2500 °C	936...4532 °F
Reset point rP	500...2498 °C	932...4528 °F
Analog start point	500...2100 °C	932...3812 °F
Analog end point	900...2500 °C	1652...4532 °F
In steps of	1 °C	1 °F
Resolution		
Resolution of switching output	[K]	1
Resolution of analog output	[K]	0.2; (+ 0.03 % of the set measuring span)
Resolution of display	[K]	1
Accuracy / deviations		
Accuracy	[K]	< ± 0.3 %; (of measured value, min. 4 K (degree of emission = 1, T = 23 °C))
Repeatability	[K]	1
Reaction times		
Response time	[ms]	2; (T > 900 °C)
Software / programming		
Adjustment of the switch point		Programming buttons
Parameter setting options		Analog range; normally open / closed; switch-on/switch-off delay; Damping; Peakhold; emissivity; simulation function
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
SIO mode		yes
Required master port class		A
Process data analog		16
Process data binary		1
Min. process cycle time	[ms]	3.6
Supported DeviceIDs		
	Type of operation	DeviceID
	default	718
Operating conditions		
Ambient temperature	[°C]	0...65
Storage temperature	[°C]	-20...80

TW2002



Infrared temperature sensor

TW-150KLBM30-KFDKG/US


Max. relative air humidity	[%]	95; (non condensing)
Protection		IP 65
Tests / approvals		
EMC		DIN EN 61000-6-2
		DIN EN 61000-6-4
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	74
Mechanical data		
Weight	[g]	455.5
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Material		threaded sleeve: stainless steel (1.4305 / 303); polyester
Lens material		tempered optical glass
Displays / operating elements		
Display		Display unit Switching status Function display Measured values
Operating elements	3	Pushbuttons
Accessories		
Items supplied		lock nuts: 2
Remarks		
Remarks		Use a screened cable to protect infrared temperature sensors from interference. The screen must be connected to the housing of the sensor via the connector.
Pack quantity		1 pcs.

Infrared temperature sensor

TW-150KLBM30-KFDKG/US

Electrical connection

Connection



OUT1: Switching output / IO-Link

OUT2: analog output

Core colors :

BK = black

BN = brown

BU = blue

GY = grey

WH = white

Connector: 1 x M12

Diagrams and graphs

