
Flow sensor with fast response time



SBY34BF0BPKG/US



Product characteristics			
Number of inputs and outputs		Number of digital outputs: 1	
Process connection		Rp 3/4	
Application			
Media Liquids; water;		Liquids; water; glycol solutions; Coolants	
Medium temperature	[°C]	085	
Pressure rating	[bar]	40	
Pressure rating	[MPa]	4	
Electrical data			
Operating voltage	[V]	1030 DC; (to SELV/PELV)	
Current consumption	[mA]	< 15	
Protection class		III	
Reverse polarity protection		yes	

Flow sensor with fast response time

SBY34BF0BPKG/US




Inputs / outputs				
Number of inputs and outputs	Number of di	gital outputs: 1		
Outputs				
Total number of outputs		1		
Output signal	switchi	ng signal		
Electrical design	P	NP		
Number of digital outputs		1		
Output function	norma	lly open		
Max. voltage drop switching [V] output DC	2	2.5		
Permanent current rating of [mA] switching output DC	1	00		
Short-circuit protection	У	es		
Overload protection	У	es		
Measuring/setting range				
Setting range [I/min]	1.	25		
Accuracy / deviations				
Repeatability		1		
[% of the final value]		1		
Hysteresis [l/min]	0,5	52		
Measuring error	-	- 5		
[% of the final value]		-		
Reaction times				
Response time [s]	< (0.01		
Operating conditions				
Ambient temperature [°C]	0.	60		
Storage temperature [°C]	-1580			
Protection	IP 65	; IP 67		
Tests / approvals				
EMC	DIN EN 61000-6-2			
	DIN EN 61000-6-3			
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)		
Vibration resistance MTTF [years]	DIN EN 60068-2-6	5 g (102000 Hz) 318		
Mechanical data				
Weight [g]		59.4		
Material	brass chemically nickel-plated; PP; aluminum anodized; PA			
Materials (wetted parts)	stainless steel (1.4310 / 301); stainless steel (1.4301 / 304); PBT; brass chemically nickel-plated; PP; PPS; Polyolefin; O-ring: FKM			
Process connection	Rp 3/4			
Switching cycles mechanical	10 r	nillion		
Displays / operating elements				
Display	Switching status	4 x LED, yellow		

Flow sensor with fast response time

SBY34BF0BPKG/US

Accessories		
Items supplied	Allen key	
Remarks		
Remarks	Caution Do not turn the cap beyond the maximum value of the setting range.	
	All data refer to water (20 °C).	
Notes	Please note the changed housing design!	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A		
3^{2}		
Connection		
	-- 1 +	



Flow sensor with fast response time

SBY34BF0BPKG/US



Diagrams and graphs Pressure loss

