

SD5100




Flow rate meter for gases

SDR14DGXFPKG/US-100

Article to be discontinued

Alternative articles: SD5600

When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit
- 2 Programming buttons
- 3 hole for fixing screw M5



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
Process connection	threaded connection G 1/4 DN8
Ar	
Measuring range [m³/h]	0.08...24.04
CO2	
Measuring range [m³/h]	0.04...14.36
N2	
Measuring range [m³/h]	0.04...15

Application

Application	for industrial applications
Media	Argon (Ar); carbon dioxide (CO2); nitrogen (N2)
Medium temperature [°C]	0...60
Pressure rating [bar]	16
Pressure rating [Mpa]	1.6

SD5100



Flow rate meter for gases

SDR14DGXFPKG/US-100

Electrical data		
Operating voltage	[V]	18...30 DC; (according to EN 50178 SELV/PELV)
Current consumption	[mA]	< 100
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analog outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analog signal; pulse signal; IO-Link; (configurable)
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250; (per output)
Number of analog outputs		1
Analog current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Pulse output		consumed quantity meter
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Low flow cut-off LFC	[m ³ /h]	< 0.26
Measuring dynamics		1:300
Ar		
Measuring range	[m ³ /h]	0.08...24.04
Display range	[m ³ /h]	0...28.84
Resolution	[m ³ /h]	0.02
Set point SP	[m ³ /h]	0.22...24.04
Reset point rP	[m ³ /h]	0.12...23.94
Analog start point ASP	[m ³ /h]	0...19.24
Analog end point AEP	[m ³ /h]	4.8...24.04
In steps of	[m ³ /h]	0.02

SD5100



Flow rate meter for gases

SDR14DGXFPKG/US-100

CO2		
Measuring range	[m ³ /h]	0.04...14.36
Display range	[m ³ /h]	0...17.24
Resolution	[m ³ /h]	0.02
Set point SP	[m ³ /h]	0.14...14.36
Reset point rP	[m ³ /h]	0.08...14.3
Analog start point ASP	[m ³ /h]	0...11.48
Analog end point AEP	[m ³ /h]	2.88...14.36
In steps of	[m ³ /h]	0.02
Volumetric flow quantity monitoring		
Pulse value		0.001...1 000 000 m ³
In steps of		0.001...1000 m ³
Pulse length	[s]	0,062...2
N2		
Measuring range	[m ³ /h]	0.04...15
Display range	[m ³ /h]	0...18
Resolution	[m ³ /h]	0.02
Set point SP	[m ³ /h]	0.14...15
Reset point rP	[m ³ /h]	0.08...14.94
Analog start point ASP	[m ³ /h]	0...12
Analog end point AEP	[m ³ /h]	3...15
In steps of	[m ³ /h]	0.02
Temperature monitoring		
Measuring range	[°C]	0...60
Display range	[°C]	-12...72
Resolution	[°C]	0.2
Set point SP	[°C]	0.4...60
Reset point rP	[°C]	0...59.8
Analog start point	[°C]	0...48
Analog end point	[°C]	12...60
In steps of	[°C]	0.2
Accuracy / deviations		
Flow monitoring		
Repeatability		± 1,5
	[% of the measured value]	
Accuracy (in the measuring range)		± (6 % MW + 0,6 % MEW); (conditions: installation to DIN ISO 2533)
Temperature monitoring		
Accuracy	[K]	± 2; (medium flow in the limit area of the flow measurement range)

SD5100



Flow rate meter for gases

SDR14DGXFPKG/US-100

Reaction times		
Flow monitoring		
Response time	[s]	0.1; (dAP = 0)
Damping for the switching output dAP in steps	[s]	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1
Software / programming		
Parameter setting options	Flow monitoring; quantity meter; Preset counter; hysteresis / window; normally open / closed; current/pulse output; display can be rotated and switched off; Display unit; medium selection	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode	yes	
Required master port class	A	
Process data analog	3	
Process data binary	2	
Min. process cycle time	[ms]	4.1
Supported DeviceIDs	Type of operation	DeviceID
	default	263
Operating conditions		
Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...85
Max. relative air humidity	[%]	90
Protection		IP 65
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
CPA approval	model number	003TG
	accuracy class	-
	maximum allowable error	± 7 % FS
	Q (min)	0,04 m³/h (N2)
		0,04 m³/h (CO2)
		0,08 m³/h (Ar)
	Q (t)	-
	Q (max)	15 m³/h (N2)
		14,36 m³/h (CO2)
		24,04 m³/h (Ar)
Vibration resistance	DIN IEC 68-2-6	5 g (55...2000 Hz)
MTTF	[years]	227
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

SD5100



Flow rate meter for gases

SDR14DGXFPKG/US-100

Mechanical data		
Weight [g]	981	
Material	PBT-GF20; PC; PC; stainless steel (1.4301 / 304); FKM	
Materials (wetted parts)	stainless steel (1.4301 / 304); ceramics glass passivated; PEEK; polyester; FKM; aluminum anodized	
Process connection	threaded connection G 1/4 DN8	
Displays / operating elements		
Display	Display unit	4 x LED, green (NI/min, Nm ³ /h, Nm ³ , °C)
	Function display	1 x LED, yellow
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit
Display unit	NI/min; Nm ³ /h; Nm ³ ; °C	
Remarks		
Remarks	MW = Measured value	
	MEW = Final value of the measuring range	
	Measuring, display and setting ranges refer to standard volume flow according to DIN ISO 2533.	
	For information about installation and operation please see the operating instructions.	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12





SD5100



Flow rate meter for gases

SDR14DGXFPKG/US-100

Connection



- OUT1: Switching output
 Pulse output quantity meter
 signal output Preset counter
- OUT2: Switching output
 analog output