

# SD8001



## Compressed air meter


SDN11DGXFPKG/US-100

Article to be discontinued

Discontinuation date: 12/31/2024

Alternative articles: SD8501

When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit  
2 Programming buttons



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
Measuring range	30...7946 scfh   1...132.4 scfm
Process connection	threaded connection 1" NPT DN25

### Application

Application	for industrial applications
Media	compressed air
Note on media	air quality ISO 8573-1 class 141 class 344
Medium temperature	[°F]
Pressure rating	[bar]
Pressure rating	[psi]
MAWP (for applications according to CRN)	[bar]

### Electrical data

Operating voltage	[V]	19...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 100
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.5

# SD8001



## Compressed air meter

SDN11DGXFPKG/US-100

Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Outputs		
Total number of outputs		2
Output signal	switching signal; analog signal; pulse signal; (configurable)	
Electrical design	PNP	
Number of digital outputs		2
Output function	normally open / closed; (configurable)	
Max. voltage drop switching output DC [V]		2
Permanent current rating of switching output DC [mA]		250; (per output)
Number of analog outputs		1
Analog current output [mA]	4...20; (scalable)	
Max. load [Ω]		500
Pulse output	consumed quantity meter	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Measuring/setting range		
Measuring range	30...7946 scfh	1...132.4 scfm
Display range	0...9535 scfh	0...158.9 scfm
Set point SP	70...7945 scfh	1.2...132.4 scfm
Reset point rP	30...7905 scfh	0.5...131.7 scfm
Analog start point ASP	0...5960 scfh	0...99.3 scfm
Analog end point AEP	1985...7945 scfh	33.1...132.4 scfm
In steps of	5 scfh	0.1 scfm
Volumetric flow quantity monitoring		
Pulse value	0.120...4 000 000 scf	
In steps of	0.020...1000 scf	
Pulse length [s]	0,045...2	
Temperature monitoring		
Measuring range [°F]		32...140
Display range [°F]		32...140
Accuracy / deviations		
Flow monitoring		
Repeatability	[% of the measured value]	± 1,5
Accuracy (in the measuring range)	± (3 % MW + 0,3 % MEW) / ± (6 % MW + 0,6 % MEW); (class 141 /; class 344; conditions: installation to DIN ISO 2533; installation in pipes: DN25)	
Temperature monitoring		
Accuracy [K]	± 2; (medium flow in the limit area of the flow measurement range)	

# SD8001

## Compressed air meter

SDN11DGXFPKG/US-100



Reaction times		
Flow monitoring		
Response time	[s]	0.1; (dAP = 0)
Damping process value dAP in steps	[s]	0 - 0,2 - 0,4 - 0,6 - 0,8 - 1
Software / programming		
Parameter setting options		Flow monitoring; quantity meter; Preset counter; hysteresis / window; normally open / closed; current/pulse output; display can be rotated and switched off; Display unit
Operating conditions		
Ambient temperature	[°F]	32...140
Storage temperature	[°F]	-4...185
Max. relative air humidity	[%]	90
Protection		IP 65
Tests / approvals		
EMC		DIN EN 61000-6-2
		DIN EN 61000-6-3
Vibration resistance		DIN EN 68000-2-6
MTTF	[years]	5 g (55...2000 Hz)
Pressure equipment directive		227
		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	1979.5
Material		PBT-GF20; NBR; PC; stainless steel (1.4306 / 304L); PTFE; brass coated; aluminum powder-coated
Materials (wetted parts)		stainless steel (1.4306 / 304L); FKM; ceramics glass passivated; PEEK GF30; polyester; aluminum
Process connection		threaded connection 1" NPT DN25
Displays / operating elements		
Display	Display unit	4 x LED, green (scfm, scfh, scf, °F)
	Function display	1 x LED, yellow
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit
Remarks		
Remarks	<p>scf = standard cubic feet scfh = standard cubic feet per hour scfm = standard cubic feet per minute MW = Measured value MEW = Final value of the measuring range Measuring, display and setting ranges refer to standard volume flow according to DIN ISO 2533. For information about installation and operation please see the operating instructions.</p>	
Pack quantity	1 pcs.	

# SD8001



## Compressed air meter



SDN11DGXFPKG/US-100

### Electrical connection

Connector: 1 x M12; coding: A



### Connection



- OUT1:      Switching output  
                Pulse output quantity meter  
                signal output Preset counter
- OUT2:      Switching output  
                analog output