
## **SF111A**

## Flow sensor for connection to an evaluation unit









Product characteristics		
Probe length L	[mm]	12
Process connection		M12 x 1
Application		
Media		Liquids; Gases
Medium temperature	[°C]	-2060
Pressure rating	[bar]	300
Liquids		
Medium temperature	[°C]	-2060
Gases		
Medium temperature	[°C]	-2060
Electrical data		
Connection to control monitor		VS2000 Exi (PTB 01 ATEX 2075)
Measuring/setting range	е	
Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2002000
Greatest sensitivity	[cm/s]	200800
Accuracy / deviations		
Max. temperature gradier medium	nt of[K/min]	15
Reaction times		
Response time	[s]	110
Liquids		
Response time	[s]	110
Gases		
Response time	[s]	110

## **SF111A**

## Flow sensor for connection to an evaluation unit





Operating condition	าร		
Ambient temperature	e [°C]	-2060	
Protection		IP 67	
Tests / approvals			
Approval		DMT 03 ATEX E 090 X; TIIS TC17434; IECEx BVS 11.0017 X	
ATEX marking		$\langle \overline{\xi_{x}} \rangle$ II 1/2G Ex ia IIC T4 Ga/Gb	
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)	
MTTF	[years]	8648	
Mechanical data			
Weight	[g]	354.5	
Housing		Threaded type	
Dimensions	[mm]	M12 x 1	
Thread designation		M12 x 1	
Material		stainless steel (1.4404 / 316L)	
Materials (wetted par	rts)	stainless steel (1.4404 / 316L)	
Process connection		M12 x 1	
Installation length EL	[mm]	27	
Remarks			
Remarks		In principle, the type test according to 94/9/EC (ATEX) only	
		takes atmospheric conditions into account (0.81.1 bar).	
		For pressures outside this range use must be assessed and approved by the user.	
		Adhere to the operating instructions and the type test certificate.	
Pack quantity		1 pcs.	
Electrical connection	on		
Cable: 6 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm <sup>2</sup>			
Connection			
		DNI	
		BN 1	
		BK 2	
		// cv	
		3	
		VS2000 Exi	
		WH 7	
		\BII H	
		8	
		9	
	Core colors :		
	rown lue		
	lack		
	hite		
GY = g	rey		