
SF121A

Flow sensor for connection to an evaluation unit



SFM12ABB/2G /6M





Product characteristic	s	
Probe length L	[mm]	12
Process connection		 M12 x 1
Application		
Media		Liquids; Gases
Medium temperature	[°C]	-2070
Pressure rating	[bar]	30
Liquids		
Medium temperature	[°C]	-2070
Gases		
Medium temperature	[°C]	-2070
Electrical data		
Connection to control m	onitor	VS2000 Exi (PTB 01 ATEX 2075)
Measuring/setting rang	ge	
Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2002000
Greatest sensitivity		
C. Culcol Schollwity	[cm/s]	200800
Accuracy / deviations	[cm/s]	200800
		200800
Accuracy / deviations Max. temperature gradie		
Accuracy / deviations Max. temperature gradie medium		
Accuracy / deviations Max. temperature gradie medium Reaction times	ent of[K/min]	15
Accuracy / deviations Max. temperature gradie medium Reaction times Response time	ent of[K/min]	15
Accuracy / deviations Max. temperature gradie medium Reaction times Response time Liquids	ent of[K/min] [s]	15 110

SF121A

Flow sensor for connection to an evaluation unit



SFM12ABB/2G /6M

Operating conditions			
Ambient temperature	[°C]	-2070	
Protection		IP 67	
Tests / approvals			
Approval		DMT 03 ATEX E091; IECEX BVS 06.0007	
ATEX marking		$\langle \overline{E_x} \rangle$ II 2G Ex ia IIC T4 Gb	
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)	
MTTF	[years]	8648	
Safety classification			
Max. internal capacitance	[nF]	1.2	
Max. internal inductance	[µH]	6	
Temperature class		Τ4	
Mechanical data			
Weight	[g]	346	
Housing		Threaded type	
Dimensions	[mm]	M12 x 1	
Thread designation		M12 x 1	
Material		stainless steel (1.4404 / 316L)	
Materials (wetted parts)		stainless steel (1.4404 / 316L)	
Process connection		M12 x 1	
Installation length EL	[mm]	27	
Remarks			
Remarks		In principle, the type test according to 94/9/EC (ATEX) only takes atmospheric conditions into account (0.81.1 bar).	
		For pressures outside this range use must be assessed and approved by the user.	
		Adhere to the operating instructions and the type test certificate.	
Pack quantity		1 pcs.	

SF121A

Flow sensor for connection to an evaluation unit




SFM12ABB/2G /6M

Electrical connection

Cable: 6 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm²

Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey