

SF1300




Flow sensor for connection to an evaluation unit

SFM12ZBB

Article no longer available - archive entry

Alternative articles: SF5300 + E40101

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Process connection	M12 x 1
--------------------	---------

Application

Application	high temperature
Media	Liquids; Gases
Pressure rating [bar]	30

Liquids

Application	high temperature
Medium temperature [°C]	0...120

Gases

Medium temperature [°C]	0...100
-------------------------	---------

Electrical data

Connection to control monitor	VS 0200
-------------------------------	---------

Measuring/setting range

Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Gases

Setting range [cm/s]	200...2000
Greatest sensitivity [cm/s]	200...800

Accuracy / deviations

Max. temperature gradient of [K/min] medium	15
---	----

Reaction times

Response time [s]	1...10
-------------------	--------

Liquids

Response time [s]	1...10
-------------------	--------


SF1300



Flow sensor for connection to an evaluation unit

SFM12ZBB

Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		Threaded type
Dimensions	[mm]	M12 x 1
Thread designation		M12 x 1
Material		stainless steel (1.4571/316Ti)
Materials (wetted parts)		stainless steel (1.4571/316Ti)
Process connection		M12 x 1
Accessories		
Items supplied		sealings: 2 x AMF 30
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, silicone; Maximum cable length: 100 m; 5 x 0.34 mm²		
Connection		



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey