
VSM101

Accelerometer

VIBRATION SENSOR





CE CA

Product characteristics				
Measuring range of vibration	[g]	-4040		
Frequency range	[Hz]	04500		
Measuring principle		capacitive		
Application				
System		screened cable; Drag chain suitability		
Electrical data				
Bias voltage DC	[V]	1116		
Operating current	[mA]	46		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
		Microelectromechanical system (MEMS)		
Type of sensor		Microelectromechanical system (MEMS)		
Type of sensor Measuring/setting range		Microelectromechanical system (MEMS)		
	[g]	Microelectromechanical system (MEMS) -4040		
Measuring/setting range	[g] [Hz]			
Measuring/setting range Measuring range of vibration		-4040		
Measuring/setting range Measuring range of vibration Frequency range		-4040 04500		
Measuring/setting range Measuring range of vibration Frequency range Measuring principle	[Hz]	-4040 04500 capacitive		
Measuring/setting range Measuring range of vibration Frequency range Measuring principle Max. transverse sensitivity Number of measurement	[Hz]	-4040 04500 capacitive 5		
Measuring/setting range Measuring range of vibration Frequency range Measuring principle Max. transverse sensitivity Number of measurement axes	[Hz]	-4040 04500 capacitive 5 3		
Measuring/setting range Measuring range of vibration Frequency range Measuring principle Max. transverse sensitivity Number of measurement axes Accuracy / deviations Accuracy	[Hz]	-4040 04500 capacitive 5		
Measuring/setting range Measuring range of vibration Frequency range Measuring principle Max. transverse sensitivity Number of measurement axes Accuracy / deviations	[Hz]	-4040 04500 capacitive 5 3		

VSM101

Accelerometer

VIBRATION SENSOR



[% of the span]

Operating conditions					
Ambient temperature	[°C]	-3085			
Storage temperature	[°C]	-30100			
Protection		IP 67; IP 68; IP 69K			
Tests / approvals					
EMC		DIN EN 61000-6-2			
		DIN EN 61000-6-3			
Shock resistance		DIN EN 60068-2-27	50 g 11 ms		
Vibration resistance		DIN EN 60068-2-6	20 g / 103000 Hz		
MTTF	[years]	529			
Mechanical data					
Weight	[g]	187.2			
Type of mounting		mounting screw			
Dimensions	[mm]	26.2	x 47.3 x 11.6		
Material		housing: stainless steel (1.4404 / 444)			
Tightening torque	[Nm]	3.5			
Drag chain suitability		yes			
Drag chain suitability		Bending radius for flexible applications	min. 10 x cable diameter		
		Bending radius for fixed installation	min. 4 x cable diameter		
Accessories					
Items supplied		socket head screw: 1 x M5 x 12			
Remarks					
Pack quantity		1 pcs.			
Electrical connection					
Cable: 3 m, PUR, Ø 4.9 mm, screened; Maximum cable length: 250 m; screen (connected to the housing); 5 x 0.14 mm ²					
brown IEPE X white IEPE Z blue GND black self-test grey IEPE Y yellow screen					