

SF2204




Flow sensor for connection to an evaluation unit

SFR14ABB/US-100

Article no longer available - archive entry

Alternative articles: SF5200 + E40099

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Process connection	G 1/4 external thread
--------------------	-----------------------

Application

Application	high temperature
Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Liquids

Application	high temperature
Medium temperature [°C]	-25...80

Gases

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Connection to control monitor	VS 0200
-------------------------------	---------

Measuring/setting range

Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Gases

Setting range [cm/s]	200...2000
Greatest sensitivity [cm/s]	200...800

Accuracy / deviations

Max. temperature gradient of [K/min] medium	15
---	----

Reaction times

Response time [s]	1...10
-------------------	--------

Liquids

Response time [s]	1...10
-------------------	--------

SF2204



Flow sensor for connection to an evaluation unit

SFR14ABB/US-100

Gases

Response time	[s]	1...10
---------------	-----	--------

Operating conditions

Protection	IP 67
------------	-------

Mechanical data

Housing	Threaded type
Material	stainless steel (1.4571/316Ti)
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	G 1/4 external thread

Accessories


Items supplied	sealings: 2 x AMF 30
----------------	----------------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 m



Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey