


# VSA005

## Accelerometer

VIBRATION SENSOR



### Product characteristics

Measuring range of vibration	[g]	-25...25
Frequency range	[Hz]	1...10000
Measuring principle		capacitive

### Application

System	screened cable; Drag chain suitability
Design	for connection to external diagnostic electronics VSE
Application	vibration detection

### Electrical data

Operating voltage	[V]	7.2...10.8 DC
Current consumption	[mA]	< 15
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Type of sensor		Microelectromechanical system (MEMS)

### Outputs

Analog current output	[mA]	0...10
Max. load	[Ω]	300

### Measuring/setting range

Measuring range of vibration	[g]	-25...25
Frequency range	[Hz]	1...10000
Measuring principle		capacitive
Sensitivity	[µA/g]	142
Number of measurement axes		1

### Accuracy / deviations

Linearity deviation	0,2 %
---------------------	-------

# VSA005



## Accelerometer

VIBRATION SENSOR

Operating conditions		
Ambient temperature	[°C]	-20...80
Note on ambient temperature		cULus: < 80 °C
Storage temperature	[°C]	-20...80
Max. relative air humidity	[%]	80; (40 °C: 50 % non condensing)
Protection		IP 67
Tests / approvals		
EMC		EN 61000-6-2 EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-20
MTTF	[years]	2660
Mechanical data		
Weight	[g]	323.5
Type of mounting		mounting screw
Material		housing: stainless steel (1.4404 / 316L)
Tightening torque	[Nm]	5
Mechanische Überlastfestigkeit	[g]	500
Drag chain suitability		yes
Drag chain suitability		Bending radius for fixed installation : min. 4 x cable diameter Bending radius for flexible applications : min. 15 x cable diameter
Accessories		
Items supplied		head cap screw: 1 x M5 x 20, Torx 15
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 10 m, PUR, Ø 4 mm, screened; Maximum cable length: 250 m; drain wire applied to the housing; 4 x 0.14 mm <sup>2</sup>		
blue		GND
black		test
brown		L+
white		Out
screen		drain wire