
SF221A

Flow sensor for connection to an evaluation unit









Product characteristics		
Probe length L	[mm]	12
Process connection		G 1/4 external thread
Application		o 1/1 o noma unoda
Media		Liquids; Gases
Medium temperature	[°C]	-2070
Pressure rating	[bar]	30
Liquids		
Medium temperature	[°C]	-2070
Gases		
Medium temperature	[°C]	-2070
Electrical data		
Connection to control monitor		VS2000 Exi (PTB 01 ATEX 2075)
Measuring/setting range	e	
Probe length L	[mm]	12
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2002000
Greatest sensitivity	[cm/s]	200800
Accuracy / deviations		
Max. temperature gradient of[K/min] medium		15
Reaction times		
Response time	[s]	110
Liquids		
Response time	[s]	110
Gases		
Response time	[s]	110

SF221A

Flow sensor for connection to an evaluation unit



SFR14ABB/2G /6M

Operating conditions		
Ambient temperature	[°C]	-2070
Protection		IP 67
Tests / approvals		
Approval		DMT 03 ATEX E091; IECEX BVS 06.0007
ATEX marking		⟨Ex⟩ II 2G Ex ia IIC T4 Gb
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)
MTTF	[years]	8648
Safety classification		
Max. internal capacitance	[nF]	1.2
Max. internal inductance	[μH]	6
Temperature class		
Mechanical data		
Weight	[g]	350
Housing		Threaded type
Material		stainless steel (1.4404 / 316L)
Materials (wetted parts)		stainless steel (1.4404 / 316L)
Process connection		G 1/4 external thread
Installation length EL	[mm]	27
Remarks		
Remarks		In principle, the type test according to 94/9/EC (ATEX) only takes atmospheric conditions into account (0.81.1 bar).
		For pressures outside this range use must be assessed and approved by the user.
		Adhere to the operating instructions and the type test certificate.
Pack quantity		1 pcs.

SF221A

Flow sensor for connection to an evaluation unit




SFR14ABB/2G /6M

Electrical connection

Cable: 6 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm²

Connection



Core colors:

 $\begin{array}{lll} \text{BN} = & \text{brown} \\ \text{BU} = & \text{blue} \\ \text{BK} = & \text{black} \\ \text{WH} = & \text{white} \\ \text{GY} = & \text{grey} \end{array}$