



- 1 Combicon connector
- 2 Ethernet interface
- 3 DIN rail adapter



Product characteristics

| | | |
|-------------------------|------|-------------|
| Frequency range | [Hz] | 0.1...12000 |
| Communication interface | | Ethernet |

Application

| | |
|-------------|--|
| Design | parameter setting via PC software VES004 |
| Application | continuous vibration monitoring |

Electrical data

| | | |
|-----------------------------|------|---|
| Operating voltage tolerance | [%] | 20 |
| Operating voltage | [V] | 24 DC; (when using the IEPE input: 24 V + 20%; IEPE = Integrated Electronics Piezo Electric) |
| Current consumption | [mA] | 200; ((24 V DC)) |
| Protection class | | III |

Inputs / outputs

| | |
|------------------------------------|---|
| Total number of inputs and outputs | 8; (configurable) |
| Number of inputs and outputs | Number of analog inputs: 2; Number of dynamic inputs: 4; Number of digital outputs: 2; Number of analog outputs: 1 |

Inputs

| | |
|-------------------------|---|
| Total number of inputs | 6 |
| Number of analog inputs | 2 |

VSE003

Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS



| | | |
|---|------------|---|
| Analog input (current) | [mA] | 4...20 |
| Resolution of analog input | | 12 |
| Number of dynamic inputs | | 4 |
| Dynamic input - signal | | 0...10 mA / IEPE / 4...20 mA |
| Dynamic input - resolution | [bit] | 16 |
| Dynamic input - frequency range | [Hz] | 0,1...12000 |
| Dynamic input - sampling rate | [kSamples] | 100 |
| Outputs | | |
| Total number of outputs | | 2 |
| Output signal | | switching signal; analog signal |
| Electrical design | | PNP |
| Number of digital outputs | | 2; (configurable) |
| Output function | | normally open / closed; (configurable) |
| Max. voltage drop switching output DC | [V] | 2 |
| Permanent current rating of switching output DC | [mA] | 100 |
| Number of analog outputs | | 1; (configurable) |
| Analog current output | [mA] | 4...20 |
| Max. load | [Ω] | 500 |
| Short-circuit protection | | yes |
| Type of short-circuit protection | | yes (non-latching) |
| Overload protection | | yes |
| Measuring/setting range | | |
| Frequency range | [Hz] | 0.1...12000 |
| Interfaces | | |
| Communication interface | | Ethernet |
| Transmission rate | | 10 MBaud; 100 MBaud |
| Protocol | | TCP/IP |
| Operating conditions | | |
| Ambient temperature | [°C] | 0...70 |
| Storage temperature | [°C] | 0...70 |
| Protection | | IP 20 |
| Tests / approvals | | |
| EMC | | EN IEC 61000-6-2 EN IEC 61000-6-4 |
| UL approval | | Ta 70 °C Enclosure type Type 1 voltage supply Limited Voltage/Current (Marking Class 2) File number UL E251902 |
| Mechanical data | | |
| Weight | [g] | 327 |

Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

| | |
|--|---|
| Housing | Plastic housing |
| Type of mounting | rail; (TH35/EN60715) |
| Dimensions [mm] | 100 x 25.4 x 103.4 |
| Material | PA |
| Data memory | |
| History memory | yes |
| Data memory buffered | yes |
| Data memory type | ring memory; FIFO |
| Real-time clock | yes |
| Memory location | internal |
| Memory interval | min. 1 min |
| Memory size | 881664 data records |
| Accessories | |
| Accessories (optional) | cross-over Ethernet patch cable for the direct connection to the PC |
| Remarks | |
| Pack quantity | 1 pcs. |
| Electrical connection | |
| Combicon: ; Maximum cable length: 250 m | |
| Connection | |
| | |
| 1 O Supply L+ (24 V DC ±20 %) 2 O Supply L- (GND) 3 O OU 1: switch/analog 4 O OU 2: switch 5 O IN 1 (0/4...20 mA / pulse) 6 O GND 1 7 O IN 2 (0/4...20 mA / pulse) 8 O GND 2 9 O 10 O 11 O 12 O | |