


SF3306



Flow sensor for connection to an evaluation unit

SFR12ADB/US-100

Article no longer available - archive entry



Product characteristics		
Process connection		G 1/2
Application		
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	300
Measuring/setting range		
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Gases		
Setting range	[cm/s]	200...2000
Greatest sensitivity	[cm/s]	200...800
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		Threaded type
Dimensions	[mm]	27 x 27 x 72
Material		stainless steel (1.4571/316Ti)
Materials (wetted parts)		stainless steel (1.4571/316Ti)
Process connection		G 1/2

SF3306




Flow sensor for connection to an evaluation unit


SFR12ADB/US-100

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 100 (5 x 0.5mm²) m



Connection



BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey