
SF5702

Flow sensor for connection to an evaluation unit



SFD10ADT /US-100





Product characteristics			
Probe length L	[mm]	93	
Process connection		M18 x 1,5 Internal thread	
Application			
Media		Liquids; Gases; aggressive media	
Medium temperature	[°C]	-2580	
Pressure rating	[bar]	100	
Electrical data			
Connection to control monitor		VS3000	
Measuring/setting range	;		
Probe length L	[mm]	93	
Liquids			
Setting range	[cm/s]	3300	
Greatest sensitivity	[cm/s]	360	
Gases			
Setting range	[cm/s]	2003000	
Greatest sensitivity	[cm/s]	200800	
Accuracy / deviations			
Max. temperature gradien medium	t of[K/min]	300	
Reaction times			
Response time	[S]	110	
Operating conditions			
Storage temperature	[°C]	-2580	
Protection		IP 67	
Tests / approvals			
Shock resistance		DIN IEC 68-2-27 50 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)	
MTTF	[years]	8393.77	

ifm efector, inc. • 1100 Atwater Drive • Malvern • PA 19355 — We reserve the right to make technical alterations without prior notice. — EN-US — SF5702-00 — 05.11.2020 — 🚊

SF5702

Flow sensor for connection to an evaluation unit



SFD10ADT /US-100

Mechanical data		
Weight	[g]	68
Housing		for adapter
Dimensions	[mm]	M18 x 1.5
Thread designation		M18 x 1.5
Material		titanium (3.7035); EPDM; ULTEM
Materials (wetted parts)		titanium (3.7035); O-ring: FKM 80 Shore A
Process connection		M18 x 1,5 Internal thread
Remarks		
Pack quantity		1 pcs.
Electrical connection		
5		
Connection		

5 GY

	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey