
## SF5704

## Flow sensor for connection to an evaluation unit



SFD10ADT /US-100





Product characteristics				
Probe length L	[mm]		243	
Process connection			M18 x 1,5 Internal thread	
Application				
Media		Li	iquids; Gases; aggressive media	
Medium temperature	[°C]		-2580	
Pressure rating	[bar]		100	
Electrical data				
Connection to control monitor			VS3000	
Measuring/setting range	e			
Probe length L	[mm]		243	
Liquids				
Setting range	[cm/s]		3300	
Greatest sensitivity	[cm/s]		360	
Gases				
Setting range	[cm/s]		2003000	
Greatest sensitivity	[cm/s]		200800	
Accuracy / deviations				
Max. temperature gradient of[K/min]		300		
medium				
Reaction times Response time	[s]		110	
· · ·	[3]		110	
Operating conditions Storage temperature	[°C]		-2580	
Protection	[ ]		-2560 IP 67	
Tests / approvals Shock resistance		DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6	10 g (552000 Hz)	
MTTF	[years]		8393.77	

ifm efector, inc. • 1100 Atwater Drive • Malvern • PA 19355 — We reserve the right to make technical alterations without prior notice. — EN-US — SF5704-00 — 05.11.2020 — 🚊

## SF5704

## Flow sensor for connection to an evaluation unit



SFD10ADT /US-100

Mechanical data		
Weight	[g]	95
Housing		for adapter
Dimensions	[mm]	M18 x 1.5
Thread designation		M18 x 1.5
Material		titanium (3.7035); EPDM; ULTEM
Materials (wetted parts)		titanium (3.7035); O-ring: FKM 80 Shore A
Process connection		M18 x 1,5 Internal thread
Remarks		
Pack quantity		1 pcs.
Electrical connection		
$5 \frac{2}{3} \frac{1}{4}$		
Connection		

3 BU

	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey