
# SF6201

## Flow sensor for connection to an evaluation unit



SFG10ABB /US-100



# 

Product characteristics		
Probe length L	[mm]	15107
Process connection		Ø 10 mm
Application		
System		gold-plated contacts
Application		high temperature
Installation		Sensor suitable for clamp fitting
Media		Liquids; Gases
Medium temperature	[°C]	-2580
Pressure rating	[bar]	30
Liquids		
Application		high temperature
Installation		Sensor suitable for clamp fitting
Medium temperature	[°C]	-2580
Gases		
Medium temperature	[°C]	-2580
Electrical data		
Connection to control monitor		VS3000
Measuring/setting range	e	
Probe length L	[mm]	15107
Liquids		
Setting range	[cm/s]	3300
Greatest sensitivity	[cm/s]	360
Gases		
Setting range	[cm/s]	2003000
Greatest sensitivity	[cm/s]	200800
Accuracy / deviations		
Max. temperature gradient of[K/min] medium		30
Reaction times		1 10
Response time	[S]	110

# SF6201

## Flow sensor for connection to an evaluation unit



SFG10ABB /US-100

Liquids			
Response time	[S]	110	
Gases			
Response time	[S]	110	
Operating conditions			
Storage temperature	[°C]	-2580	
Protection		IP 67	
Tests / approvals			
Shock resistance		DIN IEC 68-2-27 40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6 10 g (552000 Hz)	
MTTF	[years]	8393.77	
Mechanical data			
Weight	[g]	62.5	
Material		stainless steel (1.4404 / 316L) several parts, welded	
Materials (wetted parts)		stainless steel (1.4404 / 316L) several parts, welded	
Process connection		Ø 10 mm	
Accessories			
Accessories (optional)		Clamp adapter: R 1/2, E40160	
		Clamp adapter: 1/2" NPT, E40174	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
Connector: 1 x M12; codin	g: A; Conta	cts: gold-plated; Maximum cable length: 100 m	
2 1			
5 (			
3 4			


## SF6201

#### Flow sensor for connection to an evaluation unit



SFG10ABB /US-100

### Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey