



Inductive sensor

IE-2002-FROG/15M/PUR

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Sensing range [mm]	2
Housing	Threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	5...36 DC
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open / closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	no
Overload protection	no

Monitoring range

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10 \%$
Operating distance [mm]	0...1.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch-point drift [% of S_r]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

XC0073



Inductive sensor

IE-2002-FROG/15M/PUR

Tests / approvals

EMC	EN 60947-5-2	
-----	--------------	--

Mechanical data

Housing	Threaded type
Mounting	non-flush mountable
Dimensions [mm]	M8 x 1 / L = 50
Thread designation	M8 x 1
Material	PBT

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 15 m, PUR / PVC; 2 x 0.14 mm²

Connection



BK = Core colors :
WH = black
white