


SM6621



Magnetic-inductive flow meter

SMN12XGXFRKG/US-100



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1		
Measuring range	0.05...35 l/min	0.003...2.1 m³/h	0.6...555 gph
Process connection	1/2" NPT DN15		

Application

System	gold-plated contacts
Media	Conductive liquids; water; water-based media
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40°C)
Medium temperature [°F]	-4...194
Pressure rating [bar]	16
Pressure rating [MPa]	1.6

SM6621

Magnetic-inductive flow meter

SMN12XGXFRKG/US-100



Electrical data				
Operating voltage	[V]		18...30 DC; (to SELV/PELV)	
Current consumption	[mA]		< 80	
Protection class			III	
Reverse polarity protection			yes	
Power-on delay time	[s]		5	
Inputs / outputs				
Number of inputs and outputs			Number of digital outputs: 2; Number of analog outputs: 1	
Inputs				
Inputs			counter reset	
Outputs				
Total number of outputs			2	
Output signal			switching signal; analog signal; pulse signal; IO-Link; frequency signal; (configurable)	
Electrical design			PNP/NPN	
Number of digital outputs			2	
Output function			normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]		2	
Permanent current rating of switching output DC	[mA]		100	
Number of analog outputs			1	
Analog current output	[mA]		4...20; (scalable)	
Max. load	[Ω]		500	
Pulse output			flow rate meter	
Short-circuit protection			yes	
Type of short-circuit protection			yes (non-latching)	
Overload protection			yes	
Measuring/setting range				
Measuring range		0.05...35 l/min	0.003...2.1 m³/h	0.6...555 gph
Display range		-42...42 l/min	-2.5...2.5 m³/h	-666...666 gph
Resolution		0.02 l/min	0.002 m³/h	0.6 gph
Set point SP		0.25...35 l/min	0.015...2.1 m³/h	4.2...555 gph
Reset point rP		0...34.8 l/min	0...2.08 m³/h	1.2...552 gph
Analog start point ASP		0...28 l/min	0...1.7 m³/h	0...666 gph
Analog end point AEP		7...35 l/min	0.42...2.1 m³/h	111...555 gph
Low flow cut-off LFC		0.05...1.75 l/min	0.003...0.1 m³/h	0.6...27.6 gph
Frequency end point, FEP		7...35 l/min	0.42...2.1 m³/h	111.6...555 gph
Frequency at the end point FRP	[Hz]		1...10000	
Volumetric flow quantity monitoring				
Pulse length	[s]		0.001...2	
Pulse value			0.001...99990000 I	
Temperature monitoring				
Measuring range	[°F]		-4...194	

SM6621



Magnetic-inductive flow meter

SMN12XGXFRKG/US-100

Display range	[°F]	-43.6...233.6
Resolution	[°F]	0.1
Set point SP	[°F]	-3.3...194
Reset point rP	[°F]	-4...193.3
Analog start point	[°F]	-4...154.4
Analog end point	[°F]	35.6...194
In steps of	[°F]	0.1
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,2 % MEW)
Repeatability		± 0,2 % MEW
Temperature monitoring		
Accuracy	[K]	± 2,5 (Q > 5 % MEW)
Reaction times		
Flow monitoring		
Start-up delay	[s]	0...50
Response time	[s]	< 0.25; (dAP = 0, T09)
Damping process value dAP	[s]	0...5
Temperature monitoring		
Response time	[s]	15; (Q > 10 % MEW, T09)
Software / programming		
Parameter setting options		hysteresis / window; normally open / closed; switching logic; Frequency output; current/pulse output; Start-up delay; display can be deactivated; Display unit
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis
SIO mode		yes
Required master port class		A
Process data analog		3
Process data binary		2
Min. process cycle time	[ms]	6
Supported DeviceIDs	Type of operation	DeviceID
	default	952
Operating conditions		
Ambient temperature	[°F]	-4...140
Storage temperature	[°F]	-13...176
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 60947-5-9	
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)

SM6621



Magnetic-inductive flow meter

SMN12XGXFRKG/US-100


Vibration resistance	DIN IEC 68-2-6:	5 g (10...2000 Hz)		
MTTF [years]		114		
UL approval	UL approval number	I014		
	File number UL	E174189		
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data				
Weight [g]		743		
Material	stainless steel (1.4408/316); stainless steel (1.4404 / 316L); PC; PBT+PC-GF30			
Materials (wetted parts)	stainless steel (1.4404 / 316L); PEEK; carbon fiber PEEK; FKM			
Process connection	1/2" NPT DN15			
Displays / operating elements				
Display	Color display 1,44", 128 x 128 pixels 2 x LED, yellow			
Remarks				
Remarks	MW = Measured value MEW = Final value of the measuring range			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; coding: A; Contacts: gold-plated				



Magnetic-inductive flow meter

SMN12XGXFRKG/US-100

Connection



Colors to DIN EN 60947-5-2


- OUT1:
Switching output Volumetric flow quantity monitoring
Switching output Temperature monitoring
Pulse output quantity meter
Frequency output volumetric flow monitoring
Frequency output Temperature monitoring
signal output Preset counter
IO-Link
- OUT2:
Switching output Volumetric flow quantity monitoring
Switching output Temperature monitoring
analog output flow
analog output temperature
Input counter reset

Core colors :
BK = black
BN = brown
BU = blue
WH = white

Magnetic-inductive flow meter

SMN12XGXFRKG/US-100

Diagrams and graphs



Pressure loss / volumetric flow quantity