




Control monitor for flow sensors

VS0200/230VAC

Article no longer available - archive entry

Alternative articles: SN0150  
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		Flow monitoring
Electrical data		
Operating voltage tolerance	[%]	-10...10
Operating voltage	[V]	< 230 AC
Max. power consumption	[VA]	3
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design		Relay
Contact rating		4 A, 250 V AC
Switching function flow monitoring		relay energized when flow is present
Software / programming		
Adjustment of the switch point		potentiometer
Selection liquids / gases		with slide switch
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20

SN0100



Control monitor for flow sensors

VS0200/230VAC

Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Material		plastics


Displays / operating elements		
Display	Function	11 x LED

Remarks		
Pack quantity		1 pcs.

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1:
- Relais Flow monitoring
- Core colors :
- BN = brown
- BU = blue
- BK = black
- WH = white
- GY = grey