




Control monitor for flow sensors

VS0200/200VAC

Article no longer available - archive entry

Alternative articles: SN0150
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Application		Flow monitoring
Electrical data		
Operating voltage	[V]	< 200 AC
Max. power consumption	[VA]	3
Power-on delay time	[s]	30
Number of channels		1
Outputs		
Electrical design		Relay
Contact rating		4 A, 250 V AC
Switching function flow monitoring		relay energized when flow is present
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	0...60
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110

SN0117



Control monitor for flow sensors


VS0200/200VAC

Material	plastics	
Displays / operating elements		
Display	Function	11 x LED
Remarks		
Pack quantity	1 pcs.	

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Flow monitoring
- Core colors :
- BN = brown
- BU = blue
- BK = black
- WH = white
- GY = grey