




## Flow monitor

SCR14ADBFPKG/US-100-IPF

Article no longer available - archive entry

Alternative articles: SI5010 + E40099

When selecting an alternative article and accessories please note that technical data may differ!



## Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	G 1/4 external thread

## Application

Application	high pressure
Media	Liquids
Medium temperature [°C]	10...50
Pressure rating [bar]	300

## Liquids

Application	high pressure
Medium temperature [°C]	10...50

## Electrical data

Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20

## Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

## Outputs

Total number of outputs	1
-------------------------	---

# ST0566



## Flow monitor

SCR14ADBFPKG/US-100-IPF

Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	400
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

### Measuring/setting range

Liquids	
Setting range [cm/s]	100...500

### Accuracy / deviations

Max. temperature gradient of medium [K/min]	1
---	---

### Reaction times

Response time [s]	1...2
-------------------	-------

Liquids	
Response time [s]	1...2

### Software / programming

Adjustment of the switch point	potentiometer
--------------------------------	---------------

### Operating conditions

Ambient temperature [°C]	10...50
Protection	IP 67

### Mechanical data

Material	PBT-GF20
Materials (wetted parts)	stainless steel (1.4571/316Ti )
Process connection	G 1/4 external thread

### Displays / operating elements

Display	Function	11 x LED
---------	----------	----------

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Connector: 1 x M12; coding: A



# ST0566



## Flow monitor

SCR14ADBFPKG/US-100-IPF

### Connection

