


ST2606



Flow monitor

SCR14ABBFPG/6M/PH

Article no longer available - archive entry



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 1
Process connection		G 1/4 external thread
Application		
Media		Liquids
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Electrical data		
Operating voltage	[V]	20...36 DC
Current consumption	[mA]	< 45
Reverse polarity protection		yes
Power-on delay time	[s]	< 20
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2.5

ST2606



Flow monitor

SCR14ABBFPKG/6M/PH

Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Accuracy / deviations		
Max. temperature gradient of medium	[K/min]	15
Reaction times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...80
Protection		IP 67
Mechanical data		
Material		PBT-GF20
Materials (wetted parts)		stainless steel (1.4571/316Ti)
Process connection		G 1/4 external thread
Displays / operating elements		
Display	Function	11 x LED
Accessories		
Items supplied		sealings: 2 x AMF 30 screwdrivers
Remarks		
Pack quantity		1 pcs.

ST2606





Flow monitor

SCR14ABBFPKG/6M/PH

Electrical connection

Cable: 6 m, PUR; 3 x 0.5 mm²

Connection



BN =	Core colors :
BU =	brown
BK =	blue
	black