

ST3610

Flow monitor


SCN12ABAFPKG/PH



Article no longer available - archive entry

Alternative articles: SI5000 + E40127

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	1/2" NPT

Application

Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Electrical data

Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1
Output function	normally open / closed; (configurable)

ST3610



Flow monitor

SCN12ABAFPKG/PH

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Accuracy / deviations		
Max. temperature gradient of medium	[K/min]	15
Reaction times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...80
Protection		IP 67
Mechanical data		
Material		PBT-GF20
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		1/2" NPT
Displays / operating elements		
Display	Function	11 x LED
Remarks		
Pack quantity		1 pcs.

ST3610



Flow monitor

SCN12ABAFPKG/PH

Electrical connection

Cable: 2 m, PUR; 3 x 0.5 mm²

Connection



BN =
BU =
BK =

Core colors :
brown
blue
black