

ST3619




Flow monitor

SCN12ABAFNKG/US-100-INF/CSA

Article no longer available - archive entry

Alternative articles: SI5001 + E40107

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1
Process connection	1/2" NPT

Application

Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Electrical data

Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1
------------------------------	------------------------------

Outputs

Total number of outputs	1
Output signal	switching signal
Electrical design	NPN
Number of digital outputs	1
Output function	normally open / closed; (configurable)

ST3619



Flow monitor

SCN12ABAFNKG/US-100-INF/CSA

Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Measuring/setting range

Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60

Accuracy / deviations

Max. temperature gradient of medium	[K/min]	15
-------------------------------------	---------	----

Reaction times

Response time	[s]	1...10
---------------	-----	--------

Software / programming

Adjustment of the switch point		potentiometer
--------------------------------	--	---------------

Operating conditions

Ambient temperature	[°C]	-20...80
Protection		IP 67

Mechanical data

Material		PBT-GF20
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		1/2" NPT

Displays / operating elements

Display	Function	11 x LED
---------	----------	----------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A



ST3619



Flow monitor

SCN12ABAFNKG/US-100-INF/CSA

Connection

