


ST4000



Flow sensor for connection to an evaluation unit

STR34ABA

Article no longer available - archive entry



Product characteristics	
Process connection	G 3/4 external thread
Application	
Application	high temperature
Media	Liquids; Gases
Medium temperature [°C]	-25...80
Pressure rating [bar]	30
Liquids	
Application	high temperature
Medium temperature [°C]	-25...80
Gases	
Medium temperature [°C]	-25...80
Electrical data	
Connection to control monitor	VS 0100
Measuring/setting range	
Liquids	
Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60
Gases	
Setting range [cm/s]	5...1500
Accuracy / deviations	
Max. temperature gradient of [K/min] medium	15


ST4000



Flow sensor for connection to an evaluation unit

STR34ABA

Reaction times		
Response time	[s]	1...10
Liquids		
Response time	[s]	1...10
Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67
Mechanical data		
Housing		Threaded type
Material		stainless steel (1.4305 / 303)
Process connection		G 3/4 external thread
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, Silflex-PUR; Maximum cable length: 100 m; 4 x 0.5 mm ²		
Connection		



	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white