


# SV3151



## Vortex flow meter

SVR12XGXD0KG/US



### Product characteristics

Number of inputs and outputs	Number of analog outputs: 1	
Measuring range	0.5...10 l/min	0.074...1.474 m/s
Process connection	threaded connection G 1/2 external thread DN6	

### Application

Special feature	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Application	for industrial applications	
Installation	connection to pipe by means of an adapter	
Media	ultra-pure water; water; glycol solutions; Coolants	
Medium temperature [°C]	-15...125	
Min. burst pressure	32.5 bar	3.25 MPa
Note on min. burst pressure	125 °C	
Pressure rating	16 bar	1.6 MPa
Note on pressure rating	≤ 90 °C	

### Electrical data

Operating voltage [V]	8...33 DC	
-----------------------	-----------	--

# SV3151



## Vortex flow meter

SVR12XGXD0KG/US

Current consumption [mA]	< 5
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Power-on delay time [s]	< 2
Measuring principle	Vortex

### Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

### Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog current output [mA]	4...20
Max. load [Ω]	$< (U_b - 8 \text{ V}) / 20 \text{ mA}$ ; $U_b = 24 \text{ V}$ : 800

### Measuring/setting range

Measuring range	0.5...10 l/min	0.074...1.474 m/s
-----------------	----------------	-------------------

### Temperature monitoring

Internal heating temperature probe	1 K/mW
Measuring range [°C]	-15...125

### Accuracy / deviations

#### Flow monitoring

Accuracy (in the measuring range)	water	$Q < 50 \% \text{ MEW}$ : $< 1 \% \text{ MEW}$ / $Q > 50 \% \text{ MEW}$ : $< 2 \% \text{ MEW}$
	glycol solutions (35%)	$2 > v < 6 \text{ cSt}$ : $\pm 5 \% \text{ MEW}$ / $6 > v < 15 \text{ cSt}$ : $\pm 10 \% \text{ MEW}$
Repeatability	0,2; (% of the final value)	

#### Temperature monitoring

Accuracy [K]	$\pm 0,3 \pm 0,005 \times T$
--------------	------------------------------

### Reaction times

#### Flow monitoring

Response time [s]	0.28; (T09)
-------------------	-------------

#### Temperature monitoring

Dynamic response T05 / T09 [s]	< 20 / < 50
--------------------------------	-------------

### Operating conditions

Ambient temperature [°C]	-15...85
Note on ambient temperature	Medium temperature $> 0 \text{ °C}$ : -40...85
Storage temperature [°C]	-40...85
Protection	IP 65
Cavitation	$P(\text{absolute discharge}) / P(\text{difference}) > 5.5$ to avoid cavitation

### Tests / approvals

EMC	EN IEC 61326-1:2021	
Shock resistance	DIN EN 60068-2-27	30 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	with water / 10...61 Hz 1 mm
		with water / 61...2000 Hz 2 g

# SV3151



## Vortex flow meter

SVR12XGXD0KG/US

MTTF	[years]	395.9
UL approval	File number UL	E364788
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	70.6
Housing		rectangular
Dimensions	[mm]	77 x 30.2 x 52.7
Material		Housing: PPS 40% glass fiber; electronics: PC 10% glass fiber
Materials (wetted parts)		sensor: PPSU; Pipe section: PPS 40% glass fiber; sealing: EPDM
Tightening torque	[Nm]	12
Process connection		threaded connection G 1/2 external thread DN6


Remarks	
Remarks	MW = Measured value MEW = Final value of the measuring range
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



### Connection



OUT: analog output  
 T1 / T2: Pt1000  
 Colors to DIN EN 60947-5-2  
 Core colors :  
 BK = black  
 BN = brown  
 BU = blue  
 WH = white

# SV3151



## Vortex flow meter

SVR12XGXD0KG/US


### Other data

#### determination using the compensation value and the response threshold for glycol-water mixtures

determination of the compensation value Q0	[l/min]	$0.625 \times (I - 4mA) - 0.15v + 0, 15$
determination of the response threshold Qmin	[l/min]	$- 0.5 + v$
v =	kinematische Viskosität	


### Diagrams and graphs

Pressure rating



P [bar] = pressure  
T [°C] = temperature  
1 = permanent

Pressure loss



dP [mbar] = Pressure loss  
Q [l/min] = volumetric flow quantity