

## Inductive sensor

IEB3001-APOG/ 6mPPU

Article no longer available - archive entry



## Product characteristics

|                    |                 |
|--------------------|-----------------|
| Electrical design  | PNP             |
| Output function    | normally closed |
| Sensing range [mm] | 1               |
| Housing            | threaded type   |
| Dimensions [mm]    | M8 x 1 / L = 35 |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | 15; (24 V) |
| Protection class            | II         |
| Reverse polarity protection | no         |

## Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 1               |
| Permanent current rating of switching output DC [mA] | 200             |
| Switching frequency DC [Hz]                          | 750             |
| Short-circuit protection                             | no              |
| Overload protection                                  | no              |

## Detection zone

|                               |              |
|-------------------------------|--------------|
| Sensing range [mm]            | 1            |
| Real sensing range $S_r$ [mm] | $1 \pm 10\%$ |
| Operating distance [mm]       | 0...0.8      |

## Accuracy / deviations

|                                  |                                                                             |
|----------------------------------|-----------------------------------------------------------------------------|
| Correction factor                | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2 |
| Hysteresis [% of $S_r$ ]         | 1...15                                                                      |
| Switch point drift [% of $S_r$ ] | -10...10                                                                    |

## Operating conditions

|                          |          |
|--------------------------|----------|
| Ambient temperature [°C] | -25...80 |
| Protection               | IP 67    |

## Mechanical data

|         |               |
|---------|---------------|
| Housing | threaded type |
|---------|---------------|

# IE5211



## Inductive sensor

IEB3001-APOG/ 6mPPU

|                    |                                        |
|--------------------|----------------------------------------|
| Mounting           | flush mountable                        |
| Dimensions [mm]    | M8 x 1 / L = 35                        |
| Thread designation | M8 x 1                                 |
| Materials          | brass nickel-plated; sensing face: PBT |

### Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

### Accessories

|                |              |
|----------------|--------------|
| Items supplied | lock nuts: 2 |
|----------------|--------------|


### Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|

### Electrical connection

Cable: 6 m, PUR / PVC; 3 x 0.14 mm<sup>2</sup>

### Connection



BN = Core colours :  
brown  
BU = blue  
BK = black