


TA2145



Temperature transmitter

TA-150CLER14-A-ZVG/US



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1
Measuring range [°C]	-50...150
Communication interface	IO-Link
Process connection	threaded connection G 1/4
Installation length EL [mm]	150

Application

System	gold-plated contacts
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Pressure rating [bar]	300
Note on pressure rating	sensor
When mounted in adapters the specifications of the adapter data sheet apply.	

Electrical data

Operating voltage [V]	18...32 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	1

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal; IO-Link; (configurable)
Number of analog outputs	1
Analog current output [mA]	4...20
Max. load [Ω]	250; ((18...19 V); 19...32 V: 300 Ω)
Short-circuit protection	yes
Overload protection	yes

Measuring/setting range

Measuring range [°C]	-50...150
----------------------	-----------

TA2145



Temperature transmitter

TA-150CLER14-A-ZVG/US

Factory setting		-50...150 °C	
Resolution			
Resolution of analog output		[K]	0.04
Accuracy / deviations			
Precision analog output		[K]	± 0,3 + (± 0,1 % MS)
Temperature coefficient		0,1; (In case of deviation from the reference condition 25 ± 5 °C)	
[% of the span / 10 K]			
Reaction times			
Dynamic response T05 / T09		[s]	1 / 3
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
Operating conditions			
Ambient temperature		[°C]	-25...80
Storage temperature		[°C]	-40...100
Protection		IP 67; IP 68; IP 69K	
Tests / approvals			
EMC		DIN EN 61000-6-2	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF		[years]	572
UL approval		UL approval number	K002
Mechanical data			
Weight		[g]	108
Dimensions		[mm]	Ø 18.7
Material		stainless steel (1.4404 / 316L); PEI; FKM	
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM	
Tightening torque		[Nm]	35
Process connection		threaded connection G 1/4	
Probe diameter		[mm]	6
Installation length EL		[mm]	150
Displays / operating elements			
Display		operating status	1 x LED, green
Remarks			
Remarks		MS = set measuring span	
Pack quantity		1 pcs.	

TA2145



Temperature transmitter

TA-150CLER14-A-ZVG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

