


IF5923



Inductive sensor

IFG2005-ARKG/5M/UP

RT



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	5
Housing	cylindrical
Dimensions [mm]	Ø 11 / L = 38

Electrical data

Operating voltage [V]	10...36 DC
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	1
Permanent current rating of switching output DC [mA]	150
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	5
Real sensing range S_r [mm]	$5 \pm 10\%$
Operating distance [mm]	0...4.05

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]	3...15
Switch point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

IF5923



Inductive sensor

IFG2005-ARKG/5M/UP RT

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	2744

Mechanical data

Weight	[g]	189
Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 11 / L = 38
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 5 m, PVC; 2 x 0.34 mm²

Connection



BK = Core colours :
black