

TK6330




Temperature switch with intuitive switch point setting

TK6035CLFN14-QKPKG / US

Article to be discontinued

Alternative articles: TK6310

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-25...140 °C	-13...284 °F
Process connection	threaded connection 1/4" NPT	
Installation length EL [mm]	39	

Application

System	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Media	liquids and gases	
Medium temperature [°C]	-25...125; (145 max. 1 h)	
Pressure rating [bar]	300	
Minimum installation depth [mm]	15	

Electrical data

Operating voltage [V]	9.6...32 DC; (cULus - Class 2 source required)	
Current consumption [mA]	< 30	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time [s]	0.5	



Temperature switch with intuitive switch point setting

TK6035CLFN14-QKPKG / US

Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2	
Outputs		
Total number of outputs	2	
Output signal	switching signal	
Electrical design	PNP	
Number of digital outputs	2	
Output function	complementary	
Max. voltage drop switching output DC [V]	2	
Permanent current rating of switching output DC [mA]	500	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Measuring/setting range		
Probe length L [mm]	35	
Measuring range	-25...140 °C	-13...284 °F
Set point SP	-16...140 °C	3...284 °F
Reset point rP	-20...136 °C	-4...277 °F
Accuracy / deviations		
Temperature drift per 10 K [K]	0.1	
Repeatability [K]	± 0,1	
Setting accuracy [K]	± 3	
Reaction times		
Dynamic response T05 / T09 [s]	1 / 3; (according to DIN EN 60751)	
Software / programming		
Adjustment of the switch point	setting rings	
Operating conditions		
Ambient temperature [°C]	-25...70	
Storage temperature [°C]	-40...100	
Protection	IP 67	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]	485	
Mechanical data		
Weight [g]	102.5	
Material	stainless steel (1.4404 / 316L); PC; PBT; FKM	

TK6330



Temperature switch with intuitive switch point setting

TK6035CLFN14-QKPKG / US

Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	threaded connection 1/4" NPT
Installation length EL [mm]	39

Displays / operating elements


Display	Power	LED, green
	Switching status	LED, yellow
With scale		yes

Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

