
TM4591

Temperature sensor with process connection

TM-020KFER12- /US/



L = Probe length corresponds to installation length EL

CE cULus LISTED EC 1935/2004 EHEDG Tested FCM FDA

Product characteristics			
Measuring range		-40...150 °C	-40...302 °F
Process connection		threaded connection G 1/2 sealing cone	
Installation length EL	[mm]	20	
Application			
System		gold-plated contacts	
Measuring element		1 x Pt 100; (to DIN EN 60751, class A)	
Media		liquids and gases	
Pressure rating	[bar]	160	
Note on pressure rating		sensor When mounted in adapters the specifications of the adapter data sheet apply.	
Minimum installation depth	[mm]	15	
Electrical data			
Protection class		III	
Measuring/setting range			
Probe length L	[mm]	20	
Measuring range		-40...150 °C	-40...302 °F
Accuracy / deviations			
Accuracy	[K]	± (0,15 K + 0,002 x|t|)	
Reaction times			
Dynamic response T05 / T09	[s]	1 / 3; (according to DIN EN 60751)	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 68; IP 69K	
Tests / approvals			
Shock resistance		DIN EN 60068-2-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	22831.05	
Mechanical data			
Weight	[g]	132.5	

TM4591

Temperature sensor with process connection

TM-020KFER12- /US/

Material		stainless steel (1.4404 / 316L)
Materials (wetted parts)		stainless steel (1.4404 / 316L) electropolished
Tightening torque	[Nm]	30...50
Process connection		threaded connection G 1/2 sealing cone
Surface characteristics Ra/Rz of the wetted parts		Ra: < 0.8
Probe diameter	[mm]	6
Installation length EL	[mm]	20

Remarks

Remarks	cULus - Class 2 source required
	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

