

TN2531




Temperature sensor with display

TN-013KCBD10-MFRKG/US/ IV

Article to be discontinued

Alternative articles: TN2511
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1	
Measuring range	-40...150 °C	-40...302 °F
Communication interface	IO-Link	
Process connection	threaded connection M18 x 1,5 Internal thread	
Installation length EL [mm]	45	
Application		
System	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Media	liquids and gases	
Pressure rating [bar]	300	
Minimum installation depth [mm]	12	
Electrical data		
Operating voltage [V]	18...32 DC; (cULus - Class 2 source required)	



Temperature sensor with display

TN-013KCBD10-MFRKG/US/ IV

Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
------------------------------	---

Outputs

Total number of outputs		2
Output signal		switching signal; analog signal; IO-Link; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		1
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Number of analog outputs		1
Analog current output	[mA]	4...20
Max. load	[Ω]	(U _b - 10 V) x 50
Analog voltage output	[V]	0...10
Min. load resistance	[Ω]	2000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Measuring/setting range

Probe length L	[mm]	45
Measuring range	-40...150 °C	-40...302 °F
Set point SP	-39.5...150 °C	-39...302 °F
Reset point rP	-40...149.5 °C	-40...301 °F
Analog start point	-40...145 °C	-40...293 °F
Analog end point	-35...150 °C	-31...302 °F
In steps of	0.1 °C	0.1 °F

Resolution

Resolution of switching output	[K]	0.1
Resolution of analog output	[K]	0.1
Resolution of display	[K]	0.1

Accuracy / deviations

Switch point accuracy	[K]	± 0,3
Precision analog output	[K]	± 0,3
Display accuracy	[K]	± 0,3
Temperature drift per 10 K	[K]	0.1

TN2531



Temperature sensor with display

TN-013KCB10-MFRKG/US/ IV

Reaction times		
Dynamic response T05 / T09	[s]	1 / 3; (according to DIN EN 60751)
Max. measuring/display cycle	[ms]	200
Software / programming		
Adjustment of the switch point		Programming button
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.0
Operating conditions		
Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-5 Surge	1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	209
Mechanical data		
Weight	[g]	202.8
Housing		Compact type for adapter
Material		stainless steel (1.4301 / 304); PBT; PC; EPDM/X; FKM
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A
Process connection		threaded connection M18 x 1,5 Internal thread
Installation length EL	[mm]	45
Displays / operating elements		
Display	Display unit	2 x LED, green
	Switching status	LED, yellow
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit
Remarks		
Remarks		The values for accuracy apply to flowing water.
Pack quantity		1 pcs.

TN2531



Temperature sensor with display

TN-013KCBD10-MFRKG/US/ IV

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

