

TN7531




Temperature sensor with display

TN-013KBBBD10-QFPKG/US/ IV

Article to be discontinued

Alternative articles: TN7511

When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 Programming button
- 4 Internal thread M18 x 1.5



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-40...150 °C	-40...302 °F
Communication interface	IO-Link	
Process connection	threaded connection M18 x 1,5 Internal thread	
Installation length EL	[mm]	45
Application		
System	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)	
Media	liquids and gases	
Pressure rating	[bar]	300
Minimum installation depth	[mm]	12
Electrical data		
Operating voltage	[V]	18...32 DC; (cULus - Class 2 source required)

TN7531



Temperature sensor with display

TN-013KBBD10-QFPKG/US/ IV

Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Output signal	switching signal; IO-Link; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC	[V] 2
Permanent current rating of switching output DC	[mA] 250
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Measuring/setting range

Probe length L	[mm]	45
Measuring range	-40...150 °C	-40...302 °F
Set point SP	-39.5...150 °C	-39...302 °F
Reset point rP	-40...149.5 °C	-40...301 °F
In steps of	0.1 °C	0.1 °F
Resolution		
Resolution of switching output	[K]	0.1
Resolution of display	[K]	0.1

Accuracy / deviations

Switch point accuracy	[K]	± 0,3
Display accuracy	[K]	± 0,3
Temperature drift per 10 K	[K]	0.1

Reaction times

Dynamic response T05 / T09	[s]	1 / 3; (according to DIN EN 60751)
----------------------------	-----	------------------------------------

Interfaces

Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.0

Operating conditions

Ambient temperature	[°C]	-25...70
Storage temperature	[°C]	-40...100
Protection		IP 67

TN7531



Temperature sensor with display

TN-013KBBBD10-QFPKG/US/ IV

Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-5 Surge	1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	242

Mechanical data		
Weight	[g]	212.6
Housing		for adapter
Material		stainless steel (1.4301 / 304); EPDM/X; CO-PC; PBT; FKM; PA
Materials (wetted parts)		stainless steel (1.4404 / 316L); O-ring: FKM 80 Shore A
Process connection		threaded connection M18 x 1,5 Internal thread
Installation length EL	[mm]	45

Displays / operating elements		
Display	Display unit	2 x LED, green
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, 4-digit
	Programming	alphanumeric display, 4-digit

Remarks		
Remarks		The values for accuracy apply to flowing water.
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



TN7531



Temperature sensor with display

TN-013KBBD10-QFPKG/US/ IV

Connection

