

TS2151




Temperature cable sensor with process connection

TS-200KCKD8 /US/ IV

Article no longer available - archive entry

Alternative articles: TS2089 or TS2289

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Measuring range	-40...150 °C	-40...302 °F
-----------------	--------------	--------------

Application

System	gold-plated contacts
Measuring element	1 x Pt 1000; (to DIN EN 60751, class B)
Media	liquids and gases
Minimum installation depth [mm]	15

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...150 °C	-40...302 °F
-----------------	--------------	--------------

Accuracy / deviations

Accuracy [K]	$\pm (0,30 K + 0,005 \times t)$
--------------	-----------------------------------

Reaction times

Dynamic response T05 / T09 [s]	7 / 18; (according to DIN EN 60751)
--------------------------------	-------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Mechanical data

Weight [g]	113
Dimensions [mm]	Ø 8 / L = 50
Material	stainless steel; FKM
Materials (wetted parts)	stainless steel (1.4404 / 316L)
Probe diameter [mm]	8

Remarks

Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

TS2151



Temperature cable sensor with process connection

TS-200KCKD8 /US/ IV

Electrical connection

Cable: 2 m, FKM

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

