


TS5289



Temperature cable sensor with process connection

TS-500KLKD6-...../US/



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	Ø 6 mm	

Application

System	gold-plated contacts	
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)	
Media	liquids and gases	
Minimum installation depth [mm]	15	

Electrical data

Protection class	III	
------------------	-----	--

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 x t)$	
--------------	-----------------------------	--

Reaction times

Dynamic response T05 / T09 [s]	3 / 10; (according to DIN EN 60751)	
--------------------------------	-------------------------------------	--

Operating conditions

Protection	IP 67	
------------	-------	--

Tests / approvals

MTTF [years]	11415.5	
--------------	---------	--

Mechanical data

Weight [g]	180.2	
Housing	Measuring probes	
Dimensions [mm]	Ø 6 / L = 45	
Material	stainless steel	
Materials (wetted parts)	stainless steel (1.4404 / 316L)	
Process connection	Ø 6 mm	
Probe diameter [mm]	6	

Remarks

Remarks	The values for accuracy apply to flowing water.	
Pack quantity	1 pcs.	

TS5289



Temperature cable sensor with process connection

TS-500KLKD6-...../US/

Electrical connection

Cable: 5 m, PUR

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

