


Temperature transmitter

TU-025C7EU38-A-ZVG/DE



1 O-ring

Product characteristics

Number of inputs and outputs	Number of analog outputs: 1
Measuring range [°C]	0...100
Process connection	threaded connection SAE 6 external thread
Installation length EL [mm]	25

Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Pressure rating [bar]	400

Electrical data

Operating voltage [V]	8...32 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog voltage output [V]	0.5...4.5
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Overload protection	yes

TU4707




Temperature transmitter

TU-025C7EU38-A-ZVG/DE

Measuring/setting range		
Measuring range	[°C]	0...100
Resolution		
Resolution of analog output	[K]	0.1
Accuracy / deviations		
Precision analog output	[K]	$\pm 0,3 + (\pm 0,1 \% \text{ MS})$
Temperature coefficient [% of the span / 10 K]		0,1; (In case of deviation from the reference condition $25 \pm 5 \text{ °C}$)
Reaction times		
Dynamic response T05 / T09	[s]	1 / 3; (according to DIN EN 60751)
Software / programming		
Temperature range	[°C]	0...100
Operating conditions		
Ambient temperature	[°C]	-40...100
Storage temperature	[°C]	-40...100
Protection		IP 68; IP 69K
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	849
Mechanical data		
Weight	[g]	105.689
Material		stainless steel (1.4404 / 316L); PPS; FKM
Materials (wetted parts)		stainless steel (1.4404 / 316L); FKM
Process connection		threaded connection SAE 6 external thread
Probe diameter	[mm]	6
Installation length EL	[mm]	25
Remarks		
Remarks		The values for accuracy apply to flowing water.
Pack quantity		1 pcs.
Electrical connection		

Connector: 1 x DEUTSCH connector (DT04-3P)



TU4707

Temperature transmitter

TU-025C7EU38-A-ZVG/DE



Connection

